

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203813

Luminaire Tested: **MRI-DRV-FLD6C-15-L950 F6LC-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203813
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-15-L950 F6LC-M-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 5000K, 90 CRI
LEDS, 6LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1464.0 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203813
CATALOG NUMBER: MRI-DRV-FLD6C-15-L950 F6LC-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P203813

CATALOG NUMBER: MRI-DRV-FLD6C-15-L950 F6LC-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94				94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82				82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76				76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71				71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67				67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63				63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59				59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100436
5°	99482
10°	94270
15°	85585
20°	75630
25°	65381
30°	51109
35°	31340
40°	16087
45°	6388
50°	2072
55°	717
60°	614
65°	493
70°	305
75°	402
80°	0
85°	0



TEST NUMBER: P203813
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L950 F6LC-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.8	11.5
10°-20°	420.2	28.7
20°-30°	488.5	33.4
30°-40°	299.1	20.4
40°-50°	74.3	5.1
50°-60°	8.7	0.6
60°-70°	3.3	0.2
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1077.4	73.6
0°-40°	1376.5	94.0
0°-60°	1459.5	99.7
0°-90°	1464.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1464.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1832	
5°	1808	169
15°	1508	420
25°	1081	488
35°	468	299
45°	82	74
55°	8	9
65°	4	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P203813
CATALOG NUMBER: MRI-DRV-FLD6C-15-L950 F6LC-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1832.1
2.5°	1830.2
5°	1807.8
7.5°	1759.1
10°	1693.5
12.5°	1607.3
15°	1508.0
17.5°	1401.3
20°	1296.4
22.5°	1191.4
25°	1080.9
27.5°	953.5
30°	807.4
32.5°	636.9
35°	468.3
37.5°	329.7
40°	224.8
42.5°	140.5
45°	82.4
47.5°	46.8
50°	24.3
52.5°	11.3
55°	7.5
57.5°	5.6
60°	5.6
62.5°	3.8
65°	3.8
67.5°	1.9
70°	1.9
72.5°	1.9
75°	1.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)