

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203593

Luminaire Tested: **MRI-DRV-FLD6C-15-L927 F6LC-N-X-LI**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P203593  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD6C-15-L927 F6LC-N-X-LI  
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI  
LEDS, 6LBNLI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1207.1 lumens  
Efficiency: N/A  
Efficacy: 76.4 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P203593  
CATALOG NUMBER: MRI-DRV-FLD6C-15-L927 F6LC-N-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P203593  
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L927 F6LC-N-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89	89	89	89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85	85	85	85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80	80	80	80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72	72	72	72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68	68	68	68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65	65	65	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59	59	59	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	150651
5°	140881
10°	114900
15°	84552
20°	58280
25°	43267
30°	32499
35°	20264
40°	9840
45°	3372
50°	443
55°	335
60°	197
65°	233
70°	289
75°	0
80°	0
85°	0



TEST NUMBER: P203593  
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L927 F6LC-N-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	228.5	18.9
10°-20°	410.1	34.0
20°-30°	331.6	27.5
30°-40°	191.0	15.8
40°-50°	40.4	3.3
50°-60°	3.5	0.3
60°-70°	1.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	970.2	80.4
0°-40°	1161.2	96.2
0°-60°	1205.1	99.8
0°-90°	1207.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1207.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2748	
5°	2560	228
15°	1490	410
25°	715	332
35°	303	191
45°	44	40
55°	4	3
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203593  
CATALOG NUMBER: MRI-DRV-FLD6C-15-L927 F6LC-N-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2748.1
2.5°	2715.0
5°	2560.1
7.5°	2337.3
10°	2064.1
12.5°	1783.9
15°	1489.8
17.5°	1206.1
20°	999.0
22.5°	840.6
25°	715.3
27.5°	609.1
30°	513.4
32.5°	407.3
35°	302.8
37.5°	210.6
40°	137.5
42.5°	83.6
45°	43.5
47.5°	17.4
50°	5.2
52.5°	5.2
55°	3.5
57.5°	3.5
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.8
70°	1.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)