

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203663

Luminaire Tested: **MRI-DRV-FLD6C-15-L930 F6LC-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-15-L930 F6LC-W-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI
LEDS, 6LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1396.0 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203663
CATALOG NUMBER: MRI-DRV-FLD6C-15-L930 F6LC-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P203663
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L930 F6LC-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41		
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47200
5°	47182
10°	46821
15°	46510
20°	45801
25°	44755
30°	42139
35°	38133
40°	31845
45°	24398
50°	17279
55°	10896
60°	6151
65°	3995
70°	2613
75°	1906
80°	1137
85°	1132



TEST NUMBER: P203663
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L930 F6LC-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.3	5.8
10°-20°	230.8	16.5
20°-30°	338.4	24.2
30°-40°	352.1	25.2
40°-50°	243.6	17.5
50°-60°	106.1	7.6
60°-70°	32.5	2.3
70°-80°	9.7	0.7
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	650.4	46.6
0°-40°	1002.6	71.8
0°-60°	1352.3	96.9
0°-90°	1396.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1396.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	861	
5°	857	81
15°	820	231
25°	740	338
35°	570	352
45°	315	244
55°	114	106
65°	31	33
75°	9	10
85°	2	1
90°	0	



TEST NUMBER: P203663
CATALOG NUMBER: MRI-DRV-FLD6C-15-L930 F6LC-W-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	861.0
2.5°	862.8
5°	857.4
7.5°	850.2
10°	841.1
12.5°	832.1
15°	819.5
17.5°	803.1
20°	785.1
22.5°	765.2
25°	739.9
27.5°	707.3
30°	665.7
32.5°	622.2
35°	569.8
37.5°	511.9
40°	445.0
42.5°	378.1
45°	314.7
47.5°	255.0
50°	202.6
52.5°	153.8
55°	114.0
57.5°	81.4
60°	56.1
62.5°	41.6
65°	30.8
67.5°	23.5
70°	16.3
72.5°	12.7
75°	9.0
77.5°	5.4
80°	3.6
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)