

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204043

Luminaire Tested: **MRI-DRV-FLD6C-20-L940 F6LC-M-X-H**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P204043  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD6C-20-L940 F6LC-M-X-H  
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 4000K, 90 CRI  
LEDS, 6LBMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1511.9 lumens  
Efficiency: N/A  
Efficacy: 69.4 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P204043  
CATALOG NUMBER: MRI-DRV-FLD6C-20-L940 F6LC-M-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P204043  
 CATALOG NUMBER: MRI-DRV-FLD6C-20-L940 F6LC-M-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20					20					20					20		
RC	80				70					50					30					10	0	
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10			50	30	10	0
RCR																						
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106			102	102	102	100
1	113	110	107	105	111	108	105	103		104	102	100		100	99	97			97	95	94	92
2	107	102	97	93	105	100	96	92		97	93	90		94	91	88			91	89	87	85
3	101	94	88	84	99	92	88	84		90	86	82		87	84	81			85	82	80	78
4	95	87	81	76	93	86	80	76		84	79	75		82	78	74			80	76	73	72
5	90	81	75	70	88	80	74	70		78	73	69		76	72	68			75	71	68	66
6	85	75	69	64	83	75	69	64		73	68	64		72	67	63			70	66	63	61
7	80	70	64	59	79	70	64	59		68	63	59		67	62	59			66	62	58	57
8	76	66	60	55	75	65	59	55		64	59	55		63	58	55			62	58	54	53
9	72	62	56	51	71	61	55	51		60	55	51		60	55	51			59	54	51	49
10	69	58	52	48	68	58	52	48		57	52	48		56	51	48			55	51	48	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	82033
5°	80563
10°	76446
15°	71686
20°	66762
25°	61516
30°	51255
35°	36125
40°	23022
45°	13730
50°	8102
55°	5152
60°	3552
65°	2516
70°	1731
75°	1377
80°	663
85°	0



TEST NUMBER: P204043  
 CATALOG NUMBER: MRI-DRV-FLD6C-20-L940 F6LC-M-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.8	9.0
10°-20°	353.9	23.4
20°-30°	458.6	30.3
30°-40°	340.5	22.5
40°-50°	143.7	9.5
50°-60°	51.0	3.4
60°-70°	19.7	1.3
70°-80°	6.8	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	949.4	62.8
0°-40°	1289.9	85.3
0°-60°	1484.6	98.2
0°-90°	1511.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1511.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1496	
5°	1464	137
15°	1263	354
25°	1017	459
35°	540	340
45°	177	144
55°	54	51
65°	19	20
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P204043  
CATALOG NUMBER: MRI-DRV-FLD6C-20-L940 F6LC-M-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1496.4
2.5°	1492.0
5°	1464.0
7.5°	1422.9
10°	1373.3
12.5°	1319.3
15°	1263.1
17.5°	1200.5
20°	1144.4
22.5°	1086.1
25°	1017.0
27.5°	922.0
30°	809.7
32.5°	678.0
35°	539.8
37.5°	423.2
40°	321.7
42.5°	239.6
45°	177.1
47.5°	129.5
50°	95.0
52.5°	71.2
55°	53.9
57.5°	41.0
60°	32.4
62.5°	23.8
65°	19.4
67.5°	15.1
70°	10.8
72.5°	8.6
75°	6.5
77.5°	4.3
80°	2.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)