

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204213

Luminaire Tested: **MRI-DRV-FLD6C-25-L927 F6LC-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-25-L927 F6LC-W-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI
LEDS, 6LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2486.0 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204213
CATALOG NUMBER: MRI-DRV-FLD6C-25-L927 F6LC-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P204213
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L927 F6LC-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85141
5°	85929
10°	88331
15°	90540
20°	91918
25°	90017
30°	84393
35°	75456
40°	61115
45°	40431
50°	20434
55°	8621
60°	2774
65°	1090
70°	914
75°	593
80°	0
85°	0



TEST NUMBER: P204213
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L927 F6LC-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.8	6.0
10°-20°	450.3	18.1
20°-30°	678.8	27.3
30°-40°	694.8	27.9
40°-50°	404.8	16.3
50°-60°	93.0	3.7
60°-70°	11.4	0.5
70°-80°	3.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1279.0	51.4
0°-40°	1973.8	79.4
0°-60°	2471.6	99.4
0°-90°	2486.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2486.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1553	
5°	1562	150
15°	1595	450
25°	1488	679
35°	1128	695
45°	522	405
55°	90	93
65°	8	11
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P204213
CATALOG NUMBER: MRI-DRV-FLD6C-25-L927 F6LC-W-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1553.1
2.5°	1550.2
5°	1561.5
7.5°	1572.7
10°	1586.8
12.5°	1589.7
15°	1595.3
17.5°	1589.7
20°	1575.6
22.5°	1530.5
25°	1488.2
27.5°	1420.6
30°	1333.2
32.5°	1243.0
35°	1127.5
37.5°	997.7
40°	854.0
42.5°	693.4
45°	521.5
47.5°	363.6
50°	239.6
52.5°	152.2
55°	90.2
57.5°	47.9
60°	25.3
62.5°	14.1
65°	8.4
67.5°	8.4
70°	5.7
72.5°	2.8
75°	2.8
77.5°	2.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)