

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204283

Luminaire Tested: **MRI-DRV-FLD6C-25-L935 F6LC-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204283
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-25-L935 F6LC-M-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1896.0 lumens
Efficiency: N/A
Efficacy: 60.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204283
CATALOG NUMBER: MRI-DRV-FLD6C-25-L935 F6LC-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P204283
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L935 F6LC-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102865
5°	101023
10°	95862
15°	89893
20°	83716
25°	77140
30°	64276
35°	45300
40°	28868
45°	17219
50°	10166
55°	6461
60°	4451
65°	3165
70°	2180
75°	1716
80°	852
85°	0



TEST NUMBER: P204283
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L935 F6LC-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.6	9.0
10°-20°	443.8	23.4
20°-30°	575.1	30.3
30°-40°	426.9	22.5
40°-50°	180.2	9.5
50°-60°	64.0	3.4
60°-70°	24.7	1.3
70°-80°	8.6	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1190.5	62.8
0°-40°	1617.4	85.3
0°-60°	1861.6	98.2
0°-90°	1896.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1896.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1876	
5°	1836	172
15°	1584	444
25°	1275	575
35°	677	427
45°	222	180
55°	68	64
65°	24	25
75°	8	9
85°	0	1
90°	0	



TEST NUMBER: P204283
CATALOG NUMBER: MRI-DRV-FLD6C-25-L935 F6LC-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1876.4
2.5°	1870.9
5°	1835.8
7.5°	1784.3
10°	1722.1
12.5°	1654.3
15°	1583.9
17.5°	1505.4
20°	1435.0
22.5°	1361.9
25°	1275.3
27.5°	1156.1
30°	1015.4
32.5°	850.1
35°	676.9
37.5°	530.7
40°	403.4
42.5°	300.5
45°	222.1
47.5°	162.4
50°	119.2
52.5°	89.3
55°	67.6
57.5°	51.4
60°	40.6
62.5°	29.8
65°	24.4
67.5°	18.9
70°	13.6
72.5°	10.8
75°	8.1
77.5°	5.5
80°	2.7
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)