

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203883

Luminaire Tested: **MRI-DRV-FLD6C-20-L927 F6LC-N-X-H**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P203883  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD6C-20-L927 F6LC-N-X-H  
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI  
LEDS, 6LBNH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1232.1 lumens  
Efficiency: N/A  
Efficacy: 56.5 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P203883  
CATALOG NUMBER: MRI-DRV-FLD6C-20-L927 F6LC-N-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P203883  
 CATALOG NUMBER: MRI-DRV-FLD6C-20-L927 F6LC-N-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93	93	93	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87	87	87	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81	81	81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75	75	75	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61	61	61	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54	54	54	54
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51	51	51	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	86577
5°	84437
10°	77910
15°	68979
20°	59890
25°	51227
30°	42234
35°	27813
40°	14949
45°	6621
50°	2686
55°	1940
60°	1228
65°	882
70°	721
75°	487
80°	726
85°	0



TEST NUMBER: P203883  
 CATALOG NUMBER: MRI-DRV-FLD6C-20-L927 F6LC-N-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.0	11.5
10°-20°	338.7	27.5
20°-30°	388.0	31.5
30°-40°	260.7	21.2
40°-50°	74.5	6.0
50°-60°	18.2	1.5
60°-70°	6.9	0.6
70°-80°	2.7	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	868.7	70.5
0°-40°	1129.4	91.7
0°-60°	1222.1	99.2
0°-90°	1232.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1232.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1579	
5°	1534	142
15°	1215	339
25°	847	388
35°	416	261
45°	85	74
55°	20	18
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P203883  
CATALOG NUMBER: MRI-DRV-FLD6C-20-L927 F6LC-N-X-H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1579.3
2.5°	1568.1
5°	1534.4
7.5°	1473.7
10°	1399.6
12.5°	1305.2
15°	1215.4
17.5°	1121.0
20°	1026.6
22.5°	936.8
25°	846.9
27.5°	763.8
30°	667.2
32.5°	539.1
35°	415.6
37.5°	303.3
40°	208.9
42.5°	137.0
45°	85.4
47.5°	51.6
50°	31.5
52.5°	24.7
55°	20.3
57.5°	15.7
60°	11.2
62.5°	9.0
65°	6.8
67.5°	4.5
70°	4.5
72.5°	2.3
75°	2.3
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)