

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204503

Luminaire Tested: **MRI-DRV-FLD6C-30-L927 F6LC-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-30-L927 F6LC-W-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI
LEDS, 6LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2555.0 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204503
CATALOG NUMBER: MRI-DRV-FLD6C-30-L927 F6LC-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P204503
 CATALOG NUMBER: MRI-DRV-FLD6C-30-L927 F6LC-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86386
5°	86358
10°	85692
15°	85120
20°	83821
25°	81906
30°	77119
35°	69794
40°	58281
45°	44656
50°	31624
55°	19937
60°	11249
65°	7303
70°	4776
75°	3495
80°	2115
85°	2076



TEST NUMBER: P204503
 CATALOG NUMBER: MRI-DRV-FLD6C-30-L927 F6LC-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.8	5.8
10°-20°	422.3	16.5
20°-30°	619.2	24.2
30°-40°	644.5	25.2
40°-50°	445.9	17.5
50°-60°	194.1	7.6
60°-70°	59.6	2.3
70°-80°	17.8	0.7
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1190.4	46.6
0°-40°	1834.9	71.8
0°-60°	2474.9	96.9
0°-90°	2555.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2555.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1576	
5°	1569	149
15°	1500	422
25°	1354	619
35°	1043	644
45°	576	446
55°	209	194
65°	56	60
75°	16	18
85°	3	3
90°	0	



TEST NUMBER: P204503
CATALOG NUMBER: MRI-DRV-FLD6C-30-L927 F6LC-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1575.8
2.5°	1579.2
5°	1569.3
7.5°	1556.1
10°	1539.4
12.5°	1522.9
15°	1499.8
17.5°	1469.9
20°	1436.8
22.5°	1400.4
25°	1354.1
27.5°	1294.5
30°	1218.3
32.5°	1138.8
35°	1042.9
37.5°	937.0
40°	814.4
42.5°	691.9
45°	576.0
47.5°	466.8
50°	370.8
52.5°	281.5
55°	208.6
57.5°	149.0
60°	102.6
62.5°	76.2
65°	56.3
67.5°	43.1
70°	29.8
72.5°	23.2
75°	16.5
77.5°	9.9
80°	6.7
82.5°	3.3
85°	3.3
87.5°	0.0
90°	0.0

(END OF REPORT)