

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203973

Luminaire Tested: **MRI-DRV-FLD6C-20-L930 F6LC-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-20-L930 F6LC-W-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI
LEDS, 6LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2058.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203973
CATALOG NUMBER: MRI-DRV-FLD6C-20-L930 F6LC-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P203973
 CATALOG NUMBER: MRI-DRV-FLD6C-20-L930 F6LC-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69			69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70482
5°	71137
10°	73123
15°	74955
20°	76091
25°	74520
30°	69865
35°	62466
40°	50595
45°	33469
50°	16921
55°	7140
60°	2302
65°	908
70°	753
75°	487
80°	0
85°	0



TEST NUMBER: P203973
 CATALOG NUMBER: MRI-DRV-FLD6C-20-L930 F6LC-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.0	6.0
10°-20°	372.8	18.1
20°-30°	562.0	27.3
30°-40°	575.2	27.9
40°-50°	335.1	16.3
50°-60°	77.0	3.7
60°-70°	9.5	0.5
70°-80°	2.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1058.8	51.4
0°-40°	1634.0	79.4
0°-60°	2046.1	99.4
0°-90°	2058.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2058.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1286	
5°	1293	124
15°	1321	373
25°	1232	562
35°	933	575
45°	432	335
55°	75	77
65°	7	9
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203973
CATALOG NUMBER: MRI-DRV-FLD6C-20-L930 F6LC-W-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1285.7
2.5°	1283.3
5°	1292.7
7.5°	1302.0
10°	1313.6
12.5°	1316.0
15°	1320.7
17.5°	1316.0
20°	1304.3
22.5°	1267.0
25°	1232.0
27.5°	1176.0
30°	1103.7
32.5°	1029.0
35°	933.4
37.5°	826.0
40°	707.0
42.5°	574.0
45°	431.7
47.5°	301.0
50°	198.4
52.5°	126.0
55°	74.7
57.5°	39.7
60°	21.0
62.5°	11.7
65°	7.0
67.5°	7.0
70°	4.7
72.5°	2.3
75°	2.3
77.5°	2.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)