

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204633

Luminaire Tested: **MRI-DRV-FLD6C-30-L935 F6LC-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-30-L935 F6LC-W-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 6LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3077.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204633
CATALOG NUMBER: MRI-DRV-FLD6C-30-L935 F6LC-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P204633
 CATALOG NUMBER: MRI-DRV-FLD6C-30-L935 F6LC-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105381
5°	106356
10°	109333
15°	112066
20°	113766
25°	111418
30°	104459
35°	93391
40°	75642
45°	50036
50°	25296
55°	10676
60°	3443
65°	1349
70°	1122
75°	741
80°	0
85°	0



TEST NUMBER: P204633
 CATALOG NUMBER: MRI-DRV-FLD6C-30-L935 F6LC-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.4	6.0
10°-20°	557.4	18.1
20°-30°	840.2	27.3
30°-40°	860.0	27.9
40°-50°	501.0	16.3
50°-60°	115.1	3.7
60°-70°	14.1	0.5
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1583.0	51.4
0°-40°	2443.0	79.4
0°-60°	3059.2	99.4
0°-90°	3077.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3077.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1922	
5°	1933	185
15°	1975	557
25°	1842	840
35°	1396	860
45°	645	501
55°	112	115
65°	10	14
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P204633
CATALOG NUMBER: MRI-DRV-FLD6C-30-L935 F6LC-W-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1922.3
2.5°	1918.8
5°	1932.7
7.5°	1946.6
10°	1964.1
12.5°	1967.6
15°	1974.6
17.5°	1967.6
20°	1950.1
22.5°	1894.3
25°	1842.0
27.5°	1758.3
30°	1650.2
32.5°	1538.5
35°	1395.5
37.5°	1234.9
40°	1057.0
42.5°	858.2
45°	645.4
47.5°	450.0
50°	296.6
52.5°	188.4
55°	111.7
57.5°	59.3
60°	31.4
62.5°	17.4
65°	10.4
67.5°	10.4
70°	7.0
72.5°	3.5
75°	3.5
77.5°	3.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)