

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204023

Luminaire Tested: **MRI-DRV-FLD6C-20-L935 F6LC-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-20-L935 F6LC-W-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 6LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1827.1 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204023
CATALOG NUMBER: MRI-DRV-FLD6C-20-L935 F6LC-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P204023
 CATALOG NUMBER: MRI-DRV-FLD6C-20-L935 F6LC-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91	91	91	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73	73	73	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65	65	65	65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59	59	59	59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53	53	53	53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49	49	49	49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44	44	44	44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41	41	41	41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38	38	38	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61771
5°	61749
10°	61277
15°	60863
20°	59937
25°	58570
30°	55148
35°	49905
40°	41671
45°	31934
50°	22618
55°	14260
60°	8048
65°	5228
70°	3414
75°	2499
80°	1515
85°	1510



TEST NUMBER: P204023
 CATALOG NUMBER: MRI-DRV-FLD6C-20-L935 F6LC-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	5.8
10°-20°	302.0	16.5
20°-30°	442.8	24.2
30°-40°	460.8	25.2
40°-50°	318.8	17.5
50°-60°	138.8	7.6
60°-70°	42.6	2.3
70°-80°	12.8	0.7
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	851.2	46.6
0°-40°	1312.0	71.8
0°-60°	1769.7	96.9
0°-90°	1827.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1827.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1127	
5°	1122	106
15°	1072	302
25°	968	443
35°	746	461
45°	412	319
55°	149	139
65°	40	43
75°	12	13
85°	2	2
90°	0	



TEST NUMBER: P204023
CATALOG NUMBER: MRI-DRV-FLD6C-20-L935 F6LC-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1126.8
2.5°	1129.2
5°	1122.1
7.5°	1112.7
10°	1100.8
12.5°	1089.0
15°	1072.4
17.5°	1051.1
20°	1027.4
22.5°	1001.4
25°	968.3
27.5°	925.6
30°	871.2
32.5°	814.3
35°	745.7
37.5°	670.0
40°	582.3
42.5°	494.8
45°	411.9
47.5°	333.8
50°	265.2
52.5°	201.3
55°	149.2
57.5°	106.5
60°	73.4
62.5°	54.5
65°	40.3
67.5°	30.8
70°	21.3
72.5°	16.6
75°	11.8
77.5°	7.1
80°	4.8
82.5°	2.4
85°	2.4
87.5°	0.0
90°	0.0

(END OF REPORT)