

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204643

Luminaire Tested: **MRI-DRV-FLD6C-30-L940 F6LC-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204643
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-30-L940 F6LC-M-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 4000K, 90 CRI
LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2228.9 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204643
CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P204643
 CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120928
5°	118765
10°	112696
15°	105682
20°	98423
25°	90683
30°	75562
35°	53257
40°	33942
45°	20242
50°	11948
55°	7598
60°	5230
65°	3710
70°	2565
75°	2012
80°	979
85°	0



TEST NUMBER: P204643
 CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.7	9.0
10°-20°	521.8	23.4
20°-30°	676.1	30.3
30°-40°	501.9	22.5
40°-50°	211.9	9.5
50°-60°	75.2	3.4
60°-70°	29.0	1.3
70°-80°	10.0	0.5
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1399.6	62.8
0°-40°	1901.5	85.3
0°-60°	2188.6	98.2
0°-90°	2228.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2228.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2206	
5°	2158	202
15°	1862	522
25°	1499	676
35°	796	502
45°	261	212
55°	80	75
65°	29	29
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P204643
CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-M-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2205.9
2.5°	2199.5
5°	2158.2
7.5°	2097.6
10°	2024.5
12.5°	1944.9
15°	1862.1
17.5°	1769.9
20°	1687.1
22.5°	1601.1
25°	1499.2
27.5°	1359.1
30°	1193.7
32.5°	999.4
35°	795.8
37.5°	623.9
40°	474.3
42.5°	353.3
45°	261.1
47.5°	191.0
50°	140.1
52.5°	105.0
55°	79.5
57.5°	60.4
60°	47.7
62.5°	35.1
65°	28.6
67.5°	22.2
70°	16.0
72.5°	12.7
75°	9.5
77.5°	6.4
80°	3.1
82.5°	3.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)