

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204653

Luminaire Tested: **MRI-DRV-FLD6C-30-L940 F6LC-M-X-LI**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P204653  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD6C-30-L940 F6LC-M-X-LI  
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 4000K, 90 CRI  
LEDS, 6LBMLI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2727.9 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P204653  
CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-M-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P204653  
 CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-M-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	187156
5°	185373
10°	175659
15°	159479
20°	140922
25°	121834
30°	95236
35°	58404
40°	29978
45°	11908
50°	3863
55°	1329
60°	1140
65°	908
70°	561
75°	741
80°	0
85°	0



TEST NUMBER: P204653  
 CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-M-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	314.5	11.5
10°-20°	783.0	28.7
20°-30°	910.2	33.4
30°-40°	557.4	20.4
40°-50°	138.4	5.1
50°-60°	16.2	0.6
60°-70°	6.0	0.2
70°-80°	2.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2007.7	73.6
0°-40°	2565.0	94.0
0°-60°	2719.6	99.7
0°-90°	2727.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2727.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3414	
5°	3369	314
15°	2810	783
25°	2014	910
35°	873	557
45°	154	138
55°	14	16
65°	7	6
75°	4	2
85°	0	0
90°	0	



TEST NUMBER: P204653  
CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-M-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3414.0
2.5°	3410.4
5°	3368.6
7.5°	3277.8
10°	3155.6
12.5°	2995.1
15°	2810.0
17.5°	2611.1
20°	2415.6
22.5°	2220.1
25°	2014.2
27.5°	1776.8
30°	1504.5
32.5°	1186.8
35°	872.7
37.5°	614.3
40°	418.9
42.5°	261.8
45°	153.6
47.5°	87.3
50°	45.3
52.5°	21.0
55°	13.9
57.5°	10.4
60°	10.4
62.5°	7.0
65°	7.0
67.5°	3.5
70°	3.5
72.5°	3.5
75°	3.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)