

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204123

Luminaire Tested: **MRI-DRV-FLD6C-20-L950 F6LC-N-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-20-L950 F6LC-N-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 5000K, 90 CRI
LEDS, 6LBNH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1326.9 lumens
Efficiency: N/A
Efficacy: 60.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204123
CATALOG NUMBER: MRI-DRV-FLD6C-20-L950 F6LC-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P204123
 CATALOG NUMBER: MRI-DRV-FLD6C-20-L950 F6LC-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			58
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			54
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	93255
5°	90947
10°	83916
15°	74297
20°	64511
25°	55177
30°	45488
35°	29955
40°	16102
45°	7133
50°	2891
55°	2084
60°	1327
65°	947
70°	785
75°	508
80°	758
85°	0



TEST NUMBER: P204123
 CATALOG NUMBER: MRI-DRV-FLD6C-20-L950 F6LC-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.0	11.5
10°-20°	364.8	27.5
20°-30°	417.9	31.5
30°-40°	280.8	21.2
40°-50°	80.2	6.0
50°-60°	19.6	1.5
60°-70°	7.5	0.6
70°-80°	2.9	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.7	70.5
0°-40°	1216.4	91.7
0°-60°	1316.3	99.2
0°-90°	1326.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1326.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1701	
5°	1653	153
15°	1309	365
25°	912	418
35°	448	281
45°	92	80
55°	22	20
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P204123
CATALOG NUMBER: MRI-DRV-FLD6C-20-L950 F6LC-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1701.1
2.5°	1689.0
5°	1652.7
7.5°	1587.3
10°	1507.5
12.5°	1405.8
15°	1309.1
17.5°	1207.5
20°	1105.8
22.5°	1009.0
25°	912.2
27.5°	822.7
30°	718.6
32.5°	580.7
35°	447.6
37.5°	326.6
40°	225.0
42.5°	147.6
45°	92.0
47.5°	55.6
50°	33.9
52.5°	26.6
55°	21.8
57.5°	16.9
60°	12.1
62.5°	9.6
65°	7.3
67.5°	4.9
70°	4.9
72.5°	2.4
75°	2.4
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)