

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204203

Luminaire Tested: **MRI-DRV-FLD6C-25-L927 F6LC-W-X-H**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P204203  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD6C-25-L927 F6LC-W-X-H  
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI  
LEDS, 6LBWH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2176.0 lumens  
Efficiency: N/A  
Efficacy: 69.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P204203  
CATALOG NUMBER: MRI-DRV-FLD6C-25-L927 F6LC-W-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P204203  
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L927 F6LC-W-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91	91	91	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73	73	73	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65	65	65	65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59	59	59	59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53	53	53	53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49	49	49	49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44	44	44	44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41	41	41	41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38	38	38	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	73574
5°	73547
10°	72984
15°	72492
20°	71389
25°	69754
30°	65681
35°	59441
40°	49636
45°	38035
50°	26933
55°	16984
60°	9583
65°	6213
70°	4055
75°	2987
80°	1799
85°	1761



TEST NUMBER: P204203  
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L927 F6LC-W-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.8	5.8
10°-20°	359.7	16.5
20°-30°	527.4	24.2
30°-40°	548.9	25.2
40°-50°	379.7	17.5
50°-60°	165.3	7.6
60°-70°	50.7	2.3
70°-80°	15.2	0.7
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1013.8	46.6
0°-40°	1562.7	71.8
0°-60°	2107.8	96.9
0°-90°	2176.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2176.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1342	
5°	1336	127
15°	1277	360
25°	1153	527
35°	888	549
45°	491	380
55°	178	165
65°	48	51
75°	14	15
85°	3	2
90°	0	



TEST NUMBER: P204203  
CATALOG NUMBER: MRI-DRV-FLD6C-25-L927 F6LC-W-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1342.1
2.5°	1344.9
5°	1336.5
7.5°	1325.3
10°	1311.1
12.5°	1297.0
15°	1277.3
17.5°	1251.9
20°	1223.7
22.5°	1192.7
25°	1153.2
27.5°	1102.5
30°	1037.6
32.5°	969.9
35°	888.2
37.5°	798.0
40°	693.6
42.5°	589.3
45°	490.6
47.5°	397.5
50°	315.8
52.5°	239.7
55°	177.7
57.5°	126.9
60°	87.4
62.5°	64.9
65°	47.9
67.5°	36.7
70°	25.3
72.5°	19.8
75°	14.1
77.5°	8.4
80°	5.7
82.5°	2.8
85°	2.8
87.5°	0.0
90°	0.0

(END OF REPORT)