

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204263

Luminaire Tested: **MRI-DRV-FLD6C-25-L930 F6LC-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-25-L930 F6LC-W-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI
LEDS, 6LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2263.1 lumens
Efficiency: N/A
Efficacy: 71.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204263
CATALOG NUMBER: MRI-DRV-FLD6C-25-L930 F6LC-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P204263
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L930 F6LC-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41		
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76513
5°	76486
10°	75900
15°	75392
20°	74241
25°	72549
30°	68308
35°	61817
40°	51618
45°	39554
50°	28016
55°	17662
60°	9966
65°	6473
70°	4231
75°	3114
80°	1863
85°	1887



TEST NUMBER: P204263
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L930 F6LC-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	5.8
10°-20°	374.1	16.5
20°-30°	548.5	24.2
30°-40°	570.8	25.2
40°-50°	394.9	17.5
50°-60°	172.0	7.6
60°-70°	52.8	2.3
70°-80°	15.8	0.7
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1054.4	46.6
0°-40°	1625.2	71.8
0°-60°	2192.1	96.9
0°-90°	2263.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2263.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1396	
5°	1390	132
15°	1328	374
25°	1199	548
35°	924	571
45°	510	395
55°	185	172
65°	50	53
75°	15	16
85°	3	2
90°	0	



TEST NUMBER: P204263
CATALOG NUMBER: MRI-DRV-FLD6C-25-L930 F6LC-W-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1395.7
2.5°	1398.7
5°	1389.9
7.5°	1378.2
10°	1363.5
12.5°	1348.8
15°	1328.4
17.5°	1301.9
20°	1272.6
22.5°	1240.4
25°	1199.4
27.5°	1146.5
30°	1079.1
32.5°	1008.7
35°	923.7
37.5°	829.9
40°	721.3
42.5°	612.9
45°	510.2
47.5°	413.4
50°	328.5
52.5°	249.3
55°	184.8
57.5°	132.0
60°	90.9
62.5°	67.5
65°	49.9
67.5°	38.2
70°	26.4
72.5°	20.6
75°	14.7
77.5°	8.7
80°	5.9
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0

(END OF REPORT)