

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204903

Luminaire Tested: **MRI-DRV-FLD6C-35-L935 F6LC-N-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204903
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-35-L935 F6LC-N-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 6LBNH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2260.0 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204903
CATALOG NUMBER: MRI-DRV-FLD6C-35-L935 F6LC-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P204903
 CATALOG NUMBER: MRI-DRV-FLD6C-35-L935 F6LC-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			58
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			54
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158820
5°	154886
10°	142917
15°	126533
20°	109863
25°	93973
30°	77474
35°	51022
40°	27423
45°	12141
50°	4921
55°	3555
60°	2259
65°	1608
70°	1330
75°	868
80°	1294
85°	0



TEST NUMBER: P204903
 CATALOG NUMBER: MRI-DRV-FLD6C-35-L935 F6LC-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	260.5	11.5
10°-20°	621.3	27.5
20°-30°	711.7	31.5
30°-40°	478.2	21.2
40°-50°	136.6	6.0
50°-60°	33.5	1.5
60°-70°	12.7	0.6
70°-80°	4.9	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1593.5	70.5
0°-40°	2071.7	91.7
0°-60°	2241.8	99.2
0°-90°	2260.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2260.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2897	
5°	2815	261
15°	2230	621
25°	1554	712
35°	762	478
45°	157	137
55°	37	33
65°	12	13
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P204903
CATALOG NUMBER: MRI-DRV-FLD6C-35-L935 F6LC-N-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2897.1
2.5°	2876.5
5°	2814.6
7.5°	2703.3
10°	2567.4
12.5°	2394.2
15°	2229.5
17.5°	2056.4
20°	1883.2
22.5°	1718.5
25°	1553.6
27.5°	1401.1
30°	1223.9
32.5°	989.0
35°	762.4
37.5°	556.3
40°	383.2
42.5°	251.4
45°	156.6
47.5°	94.7
50°	57.7
52.5°	45.3
55°	37.2
57.5°	28.9
60°	20.6
62.5°	16.4
65°	12.4
67.5°	8.3
70°	8.3
72.5°	4.1
75°	4.1
77.5°	4.1
80°	4.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)