

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204293

Luminaire Tested: **MRI-DRV-FLD6C-25-L935 F6LC-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204293
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-25-L935 F6LC-M-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 6LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2320.0 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204293
CATALOG NUMBER: MRI-DRV-FLD6C-25-L935 F6LC-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P204293
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L935 F6LC-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159165
5°	157649
10°	149385
15°	135631
20°	119850
25°	103615
30°	80993
35°	49670
40°	25491
45°	10125
50°	3292
55°	1137
60°	976
65°	778
70°	481
75°	635
80°	0
85°	0



TEST NUMBER: P204293
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L935 F6LC-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.5	11.5
10°-20°	665.9	28.7
20°-30°	774.1	33.4
30°-40°	474.0	20.4
40°-50°	117.7	5.1
50°-60°	13.8	0.6
60°-70°	5.2	0.2
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1707.4	73.6
0°-40°	2181.4	94.0
0°-60°	2312.9	99.7
0°-90°	2320.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2320.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2903	
5°	2865	267
15°	2390	666
25°	1713	774
35°	742	474
45°	131	118
55°	12	14
65°	6	5
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P204293
CATALOG NUMBER: MRI-DRV-FLD6C-25-L935 F6LC-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2903.4
2.5°	2900.4
5°	2864.8
7.5°	2787.6
10°	2683.6
12.5°	2547.1
15°	2389.8
17.5°	2220.6
20°	2054.4
22.5°	1888.0
25°	1713.0
27.5°	1511.1
30°	1279.5
32.5°	1009.3
35°	742.2
37.5°	522.5
40°	356.2
42.5°	222.6
45°	130.6
47.5°	74.2
50°	38.6
52.5°	17.8
55°	11.9
57.5°	8.9
60°	8.9
62.5°	6.0
65°	6.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)