

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204353

Luminaire Tested: **MRI-DRV-FLD6C-25-L940 F6LC-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204353
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-25-L940 F6LC-M-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 4000K, 90 CRI
LEDS, 6LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2324.1 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204353
CATALOG NUMBER: MRI-DRV-FLD6C-25-L940 F6LC-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P204353
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L940 F6LC-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159439
5°	157918
10°	149647
15°	135863
20°	120055
25°	103790
30°	81133
35°	49757
40°	25541
45°	10148
50°	3292
55°	1137
60°	976
65°	778
70°	481
75°	635
80°	0
85°	0



TEST NUMBER: P204353
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L940 F6LC-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.9	11.5
10°-20°	667.0	28.7
20°-30°	775.4	33.4
30°-40°	474.9	20.4
40°-50°	117.9	5.1
50°-60°	13.8	0.6
60°-70°	5.2	0.2
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1710.4	73.6
0°-40°	2185.2	94.0
0°-60°	2316.9	99.7
0°-90°	2324.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2324.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2908	
5°	2870	268
15°	2394	667
25°	1716	775
35°	744	475
45°	131	118
55°	12	14
65°	6	5
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P204353
CATALOG NUMBER: MRI-DRV-FLD6C-25-L940 F6LC-M-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2908.4
2.5°	2905.4
5°	2869.7
7.5°	2792.4
10°	2688.3
12.5°	2551.5
15°	2393.9
17.5°	2224.4
20°	2057.9
22.5°	1891.3
25°	1715.9
27.5°	1513.7
30°	1281.7
32.5°	1011.1
35°	743.5
37.5°	523.4
40°	356.9
42.5°	223.0
45°	130.9
47.5°	74.4
50°	38.6
52.5°	17.9
55°	11.9
57.5°	8.9
60°	8.9
62.5°	6.0
65°	6.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)