

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204383

Luminaire Tested: **MRI-DRV-FLD6C-25-L940 F6LC-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-25-L940 F6LC-W-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 4000K, 90 CRI
LEDS, 6LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2298.0 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204383
CATALOG NUMBER: MRI-DRV-FLD6C-25-L940 F6LC-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P204383
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L940 F6LC-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77697
5°	77669
10°	77075
15°	76555
20°	75391
25°	73668
30°	69365
35°	62774
40°	52420
45°	40167
50°	28443
55°	17930
60°	10120
65°	6564
70°	4296
75°	3156
80°	1894
85°	1887



TEST NUMBER: P204383
 CATALOG NUMBER: MRI-DRV-FLD6C-25-L940 F6LC-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.9	5.8
10°-20°	379.9	16.5
20°-30°	556.9	24.2
30°-40°	579.6	25.2
40°-50°	401.0	17.5
50°-60°	174.6	7.6
60°-70°	53.5	2.3
70°-80°	16.1	0.7
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1070.7	46.6
0°-40°	1650.3	71.8
0°-60°	2226.0	96.9
0°-90°	2298.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2298.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1417	
5°	1411	134
15°	1349	380
25°	1218	557
35°	938	580
45°	518	401
55°	188	175
65°	51	54
75°	15	16
85°	3	2
90°	0	



TEST NUMBER: P204383
CATALOG NUMBER: MRI-DRV-FLD6C-25-L940 F6LC-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1417.3
2.5°	1420.3
5°	1411.4
7.5°	1399.6
10°	1384.6
12.5°	1369.7
15°	1348.9
17.5°	1322.1
20°	1292.3
22.5°	1259.5
25°	1217.9
27.5°	1164.3
30°	1095.8
32.5°	1024.3
35°	938.0
37.5°	842.7
40°	732.5
42.5°	622.3
45°	518.1
47.5°	419.8
50°	333.5
52.5°	253.2
55°	187.6
57.5°	134.0
60°	92.3
62.5°	68.5
65°	50.6
67.5°	38.7
70°	26.8
72.5°	20.9
75°	14.9
77.5°	8.9
80°	6.0
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0

(END OF REPORT)