

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204993

Luminaire Tested: **MRI-DRV-FLD6C-35-L940 F6LC-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204993
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-35-L940 F6LC-W-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 4000K, 90 CRI
LEDS, 6LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3637.0 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204993
CATALOG NUMBER: MRI-DRV-FLD6C-35-L940 F6LC-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P204993
 CATALOG NUMBER: MRI-DRV-FLD6C-35-L940 F6LC-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	96	94
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92	92	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76	76	76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69	69	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63	63	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57	57	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52	52	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48	48	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44	44	44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124557
5°	125710
10°	129228
15°	132464
20°	134470
25°	131693
30°	123468
35°	110390
40°	89410
45°	59146
50°	29892
55°	12616
60°	4068
65°	1596
70°	1330
75°	890
80°	0
85°	0



TEST NUMBER: P204993
 CATALOG NUMBER: MRI-DRV-FLD6C-35-L940 F6LC-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.2	6.0
10°-20°	658.8	18.1
20°-30°	993.1	27.3
30°-40°	1016.5	27.9
40°-50°	592.2	16.3
50°-60°	136.1	3.7
60°-70°	16.7	0.5
70°-80°	4.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1871.1	51.4
0°-40°	2887.7	79.4
0°-60°	3615.9	99.4
0°-90°	3637.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3637.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2272	
5°	2284	219
15°	2334	659
25°	2177	993
35°	1650	1017
45°	763	592
55°	132	136
65°	12	17
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P204993
CATALOG NUMBER: MRI-DRV-FLD6C-35-L940 F6LC-W-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2272.1
2.5°	2268.0
5°	2284.4
7.5°	2300.9
10°	2321.5
12.5°	2325.7
15°	2334.0
17.5°	2325.7
20°	2305.0
22.5°	2239.1
25°	2177.2
27.5°	2078.3
30°	1950.5
32.5°	1818.5
35°	1649.5
37.5°	1459.7
40°	1249.4
42.5°	1014.4
45°	762.9
47.5°	531.9
50°	350.5
52.5°	222.7
55°	132.0
57.5°	70.1
60°	37.1
62.5°	20.6
65°	12.3
67.5°	12.3
70°	8.3
72.5°	4.2
75°	4.2
77.5°	4.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)