

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P205113

Luminaire Tested: **MRI-DRV-FLD6C-40-L927 F6LC-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P205113
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-40-L927 F6LC-W-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI
LEDS, 6LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3998.0 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P205113
CATALOG NUMBER: MRI-DRV-FLD6C-40-L927 F6LC-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P205113
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L927 F6LC-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76	76	76	76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69	69	69	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63	63	63	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57	57	57	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52	52	52	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48	48	48	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136924
5°	138190
10°	142054
15°	145608
20°	147818
25°	144764
30°	135723
35°	121345
40°	98284
45°	65015
50°	32860
55°	13868
60°	4473
65°	1751
70°	1459
75°	974
80°	0
85°	0



TEST NUMBER: P205113
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L927 F6LC-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.9	6.0
10°-20°	724.2	18.1
20°-30°	1091.7	27.3
30°-40°	1117.4	27.9
40°-50°	651.0	16.3
50°-60°	149.6	3.7
60°-70°	18.4	0.5
70°-80°	4.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2056.9	51.4
0°-40°	3174.3	79.4
0°-60°	3974.8	99.4
0°-90°	3998.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3998.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2498	
5°	2511	241
15°	2566	724
25°	2393	1092
35°	1813	1117
45°	839	651
55°	145	150
65°	14	18
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P205113
CATALOG NUMBER: MRI-DRV-FLD6C-40-L927 F6LC-W-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2497.7
2.5°	2493.1
5°	2511.2
7.5°	2529.3
10°	2551.9
12.5°	2556.5
15°	2565.6
17.5°	2556.5
20°	2533.8
22.5°	2461.3
25°	2393.3
27.5°	2284.6
30°	2144.1
32.5°	1999.0
35°	1813.2
37.5°	1604.6
40°	1373.4
42.5°	1115.1
45°	838.6
47.5°	584.7
50°	385.3
52.5°	244.8
55°	145.1
57.5°	77.1
60°	40.8
62.5°	22.7
65°	13.5
67.5°	13.5
70°	9.1
72.5°	4.6
75°	4.6
77.5°	4.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)