

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204683

Luminaire Tested: **MRI-DRV-FLD6C-30-L940 F6LC-W-X-H**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P204683  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD6C-30-L940 F6LC-W-X-H  
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 4000K, 90 CRI  
LEDS, 6LBWH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2698.0 lumens  
Efficiency: N/A  
Efficacy: 85.4 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P204683  
CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-W-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P204683  
 CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-W-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41		
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	91221
5°	91190
10°	90490
15°	89881
20°	88511
25°	86491
30°	81437
35°	73702
40°	61544
45°	47160
50°	33398
55°	21055
60°	11874
65°	7705
70°	5033
75°	3707
80°	2210
85°	2201



TEST NUMBER: P204683  
 CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-W-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.2	5.8
10°-20°	446.0	16.5
20°-30°	653.9	24.2
30°-40°	680.5	25.2
40°-50°	470.9	17.5
50°-60°	205.0	7.6
60°-70°	62.8	2.3
70°-80°	18.8	0.7
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1257.0	46.6
0°-40°	1937.6	71.8
0°-60°	2613.4	96.9
0°-90°	2698.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2698.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1664	
5°	1657	157
15°	1584	446
25°	1430	654
35°	1101	681
45°	608	471
55°	220	205
65°	59	63
75°	18	19
85°	4	3
90°	0	



TEST NUMBER: P204683  
CATALOG NUMBER: MRI-DRV-FLD6C-30-L940 F6LC-W-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1664.0
2.5°	1667.5
5°	1657.1
7.5°	1643.2
10°	1625.6
12.5°	1608.1
15°	1583.7
17.5°	1552.2
20°	1517.2
22.5°	1478.8
25°	1429.9
27.5°	1366.9
30°	1286.5
32.5°	1202.6
35°	1101.3
37.5°	989.4
40°	860.0
42.5°	730.7
45°	608.3
47.5°	492.9
50°	391.6
52.5°	297.2
55°	220.3
57.5°	157.3
60°	108.3
62.5°	80.4
65°	59.4
67.5°	45.5
70°	31.4
72.5°	24.5
75°	17.5
77.5°	10.4
80°	7.0
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0

(END OF REPORT)