

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204763

Luminaire Tested: **MRI-DRV-FLD6C-35-L927 F6LC-M-X-H**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P204763  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD6C-35-L927 F6LC-M-X-H  
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI  
LEDS, 6LBMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2492.0 lumens  
Efficiency: N/A  
Efficacy: 61.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 40.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P204763  
CATALOG NUMBER: MRI-DRV-FLD6C-35-L927 F6LC-M-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P204763  
 CATALOG NUMBER: MRI-DRV-FLD6C-35-L927 F6LC-M-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 95  | 94  | 92  |    |    |    |
| 2   | 107 | 102 | 97  | 93  | 105 | 100 | 96  | 92  | 97  | 93  | 90  | 94  | 91  | 88  | 91  | 89  | 87  | 85  |    |    |    |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 84  | 90  | 86  | 82  | 87  | 84  | 81  | 85  | 82  | 80  | 78  |    |    |    |
| 4   | 95  | 87  | 81  | 76  | 93  | 86  | 80  | 76  | 84  | 79  | 75  | 82  | 78  | 74  | 80  | 76  | 73  | 72  |    |    |    |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  | 76  | 72  | 68  | 75  | 71  | 68  | 66  |    |    |    |
| 6   | 85  | 75  | 69  | 64  | 83  | 75  | 69  | 64  | 73  | 68  | 64  | 72  | 67  | 63  | 70  | 66  | 63  | 61  |    |    |    |
| 7   | 80  | 70  | 64  | 59  | 79  | 70  | 64  | 59  | 68  | 63  | 59  | 67  | 62  | 59  | 66  | 62  | 58  | 57  |    |    |    |
| 8   | 76  | 66  | 60  | 55  | 75  | 65  | 59  | 55  | 64  | 59  | 55  | 63  | 58  | 55  | 62  | 58  | 54  | 53  |    |    |    |
| 9   | 72  | 62  | 56  | 51  | 71  | 61  | 55  | 51  | 60  | 55  | 51  | 60  | 55  | 51  | 59  | 54  | 51  | 49  |    |    |    |
| 10  | 69  | 58  | 52  | 48  | 68  | 58  | 52  | 48  | 57  | 52  | 48  | 56  | 51  | 48  | 55  | 51  | 48  | 46  |    |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 135198 |
| 5°  | 132775 |
| 10° | 125994 |
| 15° | 118151 |
| 20° | 110032 |
| 25° | 101383 |
| 30° | 84475  |
| 35° | 59541  |
| 40° | 37943  |
| 45° | 22630  |
| 50° | 13356  |
| 55° | 8497   |
| 60° | 5855   |
| 65° | 4151   |
| 70° | 2853   |
| 75° | 2266   |
| 80° | 1105   |
| 85° | 0      |



TEST NUMBER: P204763  
 CATALOG NUMBER: MRI-DRV-FLD6C-35-L927 F6LC-M-X-H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 225.5  | 9.0       |
| 10°-20°   | 583.3  | 23.4      |
| 20°-30°   | 755.8  | 30.3      |
| 30°-40°   | 561.2  | 22.5      |
| 40°-50°   | 236.9  | 9.5       |
| 50°-60°   | 84.1   | 3.4       |
| 60°-70°   | 32.5   | 1.3       |
| 70°-80°   | 11.3   | 0.5       |
| 80°-90°   | 1.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1564.7 | 62.8      |
| 0°-40°    | 2125.8 | 85.3      |
| 0°-60°    | 2446.9 | 98.2      |
| 0°-90°    | 2492.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2492.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2466 |      |
| 5°  | 2413 | 225  |
| 15° | 2082 | 583  |
| 25° | 1676 | 756  |
| 35° | 890  | 561  |
| 45° | 292  | 237  |
| 55° | 89   | 84   |
| 65° | 32   | 32   |
| 75° | 11   | 11   |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P204763  
CATALOG NUMBER: MRI-DRV-FLD6C-35-L927 F6LC-M-X-H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2466.2 |
| 2.5°  | 2459.1 |
| 5°    | 2412.8 |
| 7.5°  | 2345.1 |
| 10°   | 2263.4 |
| 12.5° | 2174.3 |
| 15°   | 2081.8 |
| 17.5° | 1978.7 |
| 20°   | 1886.1 |
| 22.5° | 1790.0 |
| 25°   | 1676.1 |
| 27.5° | 1519.5 |
| 30°   | 1334.5 |
| 32.5° | 1117.4 |
| 35°   | 889.7  |
| 37.5° | 697.5  |
| 40°   | 530.2  |
| 42.5° | 395.0  |
| 45°   | 291.9  |
| 47.5° | 213.5  |
| 50°   | 156.6  |
| 52.5° | 117.4  |
| 55°   | 88.9   |
| 57.5° | 67.6   |
| 60°   | 53.4   |
| 62.5° | 39.2   |
| 65°   | 32.0   |
| 67.5° | 24.9   |
| 70°   | 17.8   |
| 72.5° | 14.2   |
| 75°   | 10.7   |
| 77.5° | 7.2    |
| 80°   | 3.5    |
| 82.5° | 3.5    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)