

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P204883

Luminaire Tested: **MRI-DRV-FLD6C-35-L935 F6LC-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P204883
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-35-L935 F6LC-M-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2627.1 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P204883
CATALOG NUMBER: MRI-DRV-FLD6C-35-L935 F6LC-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P204883

CATALOG NUMBER: MRI-DRV-FLD6C-35-L935 F6LC-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			20	
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142521
5°	139973
10°	132819
15°	124552
20°	115994
25°	106875
30°	89052
35°	62767
40°	40004
45°	23855
50°	14081
55°	8955
60°	6173
65°	4384
70°	3013
75°	2393
80°	1168
85°	0



TEST NUMBER: P204883
 CATALOG NUMBER: MRI-DRV-FLD6C-35-L935 F6LC-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.7	9.0
10°-20°	615.0	23.4
20°-30°	796.8	30.3
30°-40°	591.6	22.5
40°-50°	249.7	9.5
50°-60°	88.7	3.4
60°-70°	34.2	1.3
70°-80°	11.9	0.5
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1649.5	62.8
0°-40°	2241.0	85.3
0°-60°	2579.4	98.2
0°-90°	2627.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2627.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2600	
5°	2544	238
15°	2195	615
25°	1767	797
35°	938	592
45°	308	250
55°	94	89
65°	34	34
75°	11	12
85°	0	2
90°	0	



TEST NUMBER: P204883
CATALOG NUMBER: MRI-DRV-FLD6C-35-L935 F6LC-M-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2599.8
2.5°	2592.3
5°	2543.6
7.5°	2472.2
10°	2386.0
12.5°	2292.1
15°	2194.6
17.5°	2085.9
20°	1988.3
22.5°	1887.0
25°	1766.9
27.5°	1601.8
30°	1406.8
32.5°	1177.9
35°	937.9
37.5°	735.3
40°	559.0
42.5°	416.4
45°	307.7
47.5°	225.1
50°	165.1
52.5°	123.8
55°	93.7
57.5°	71.2
60°	56.3
62.5°	41.3
65°	33.8
67.5°	26.2
70°	18.8
72.5°	15.0
75°	11.3
77.5°	7.6
80°	3.7
82.5°	3.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)