

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P205223

Luminaire Tested: **MRI-DRV-FLD6C-40-L935 F6LC-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P205223
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-40-L935 F6LC-W-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 6LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3690.0 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P205223
CATALOG NUMBER: MRI-DRV-FLD6C-40-L935 F6LC-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P205223
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L935 F6LC-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124765
5°	124719
10°	123762
15°	122929
20°	121058
25°	118289
30°	111378
35°	100800
40°	84172
45°	64495
50°	45679
55°	28797
60°	16249
65°	10546
70°	6892
75°	5062
80°	3031
85°	3019



TEST NUMBER: P205223
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L935 F6LC-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.0	5.8
10°-20°	609.9	16.5
20°-30°	894.3	24.2
30°-40°	930.8	25.2
40°-50°	644.0	17.5
50°-60°	280.4	7.6
60°-70°	86.0	2.3
70°-80°	25.8	0.7
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1719.2	46.6
0°-40°	2650.0	71.8
0°-60°	3574.3	96.9
0°-90°	3690.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3690.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2276	
5°	2266	215
15°	2166	610
25°	1956	894
35°	1506	931
45°	832	644
55°	301	280
65°	81	86
75°	24	26
85°	5	4
90°	0	



TEST NUMBER: P205223
CATALOG NUMBER: MRI-DRV-FLD6C-40-L935 F6LC-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2275.9
2.5°	2280.7
5°	2266.4
7.5°	2247.3
10°	2223.3
12.5°	2199.4
15°	2166.0
17.5°	2122.9
20°	2075.1
22.5°	2022.5
25°	1955.6
27.5°	1869.5
30°	1759.5
32.5°	1644.7
35°	1506.2
37.5°	1353.2
40°	1176.2
42.5°	999.3
45°	831.9
47.5°	674.1
50°	535.6
52.5°	406.5
55°	301.3
57.5°	215.2
60°	148.2
62.5°	110.0
65°	81.3
67.5°	62.2
70°	43.0
72.5°	33.5
75°	23.9
77.5°	14.3
80°	9.6
82.5°	4.8
85°	4.8
87.5°	0.0
90°	0.0

(END OF REPORT)