

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P205304

Luminaire Tested: **MRI-DRV-FLD6C-40-L950 F6LC-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P205304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-40-L950 F6LC-M-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 5000K, 90 CRI
LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3116.0 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P205304
CATALOG NUMBER: MRI-DRV-FLD6C-40-L950 F6LC-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P205304
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L950 F6LC-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92				92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66				66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61				61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57				57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53				53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49				49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169054
5°	166024
10°	157546
15°	147736
20°	137585
25°	126769
30°	105630
35°	74452
40°	47446
45°	28298
50°	16699
55°	10628
60°	7313
65°	5189
70°	3574
75°	2817
80°	1389
85°	0



TEST NUMBER: P205304
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L950 F6LC-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.0	9.0
10°-20°	729.4	23.4
20°-30°	945.1	30.3
30°-40°	701.7	22.5
40°-50°	296.2	9.5
50°-60°	105.2	3.4
60°-70°	40.6	1.3
70°-80°	14.0	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1956.5	62.8
0°-40°	2658.2	85.3
0°-60°	3059.6	98.2
0°-90°	3116.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3116.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3084	
5°	3017	282
15°	2603	729
25°	2096	945
35°	1112	702
45°	365	296
55°	111	105
65°	40	41
75°	13	14
85°	0	2
90°	0	



TEST NUMBER: P205304
CATALOG NUMBER: MRI-DRV-FLD6C-40-L950 F6LC-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3083.8
2.5°	3074.8
5°	3017.0
7.5°	2932.4
10°	2830.2
12.5°	2718.8
15°	2603.1
17.5°	2474.1
20°	2358.4
22.5°	2238.3
25°	2095.8
27.5°	1900.0
30°	1668.7
32.5°	1397.2
35°	1112.5
37.5°	872.2
40°	663.0
42.5°	493.9
45°	365.0
47.5°	267.0
50°	195.8
52.5°	146.8
55°	111.2
57.5°	84.5
60°	66.7
62.5°	49.0
65°	40.0
67.5°	31.1
70°	22.3
72.5°	17.7
75°	13.3
77.5°	9.0
80°	4.4
82.5°	4.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)