

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P205334

Luminaire Tested: **MRI-DRV-FLD6C-40-L950 F6LC-N-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P205334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-40-L950 F6LC-N-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 5000K, 90 CRI
LEDS, 6LBNLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3390.0 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P205334
CATALOG NUMBER: MRI-DRV-FLD6C-40-L950 F6LC-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P205334
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L950 F6LC-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89		
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85		
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80		
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76		
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72		
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68		
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65		
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62		
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	423113
5°	395685
10°	322712
15°	237470
20°	163680
25°	121519
30°	91274
35°	56918
40°	27630
45°	9482
50°	1245
55°	937
60°	537
65°	636
70°	785
75°	0
80°	0
85°	0



TEST NUMBER: P205334
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L950 F6LC-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	641.7	18.9
10°-20°	1151.8	34.0
20°-30°	931.3	27.5
30°-40°	536.5	15.8
40°-50°	113.4	3.3
50°-60°	9.8	0.3
60°-70°	4.9	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2724.8	80.4
0°-40°	3261.3	96.2
0°-60°	3384.5	99.8
0°-90°	3390.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3390.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7718	
5°	7190	642
15°	4184	1152
25°	2009	931
35°	850	536
45°	122	113
55°	10	10
65°	5	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P205334
CATALOG NUMBER: MRI-DRV-FLD6C-40-L950 F6LC-N-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7718.2
2.5°	7625.5
5°	7190.4
7.5°	6564.7
10°	5797.3
12.5°	5010.3
15°	4184.2
17.5°	3387.5
20°	2805.7
22.5°	2361.0
25°	2009.0
27.5°	1710.9
30°	1441.9
32.5°	1143.9
35°	850.5
37.5°	591.4
40°	386.1
42.5°	234.7
45°	122.3
47.5°	48.8
50°	14.6
52.5°	14.6
55°	9.8
57.5°	9.8
60°	4.9
62.5°	4.9
65°	4.9
67.5°	4.9
70°	4.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)