

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P205083

Luminaire Tested: **MRI-DRV-FLD6C-40-L927 F6LC-N-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P205083
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-40-L927 F6LC-N-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI
LEDS, 6LBNH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2488.1 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P205083
CATALOG NUMBER: MRI-DRV-FLD6C-40-L927 F6LC-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P205083
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L927 F6LC-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			58
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			54
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174843
5°	170515
10°	157334
15°	139297
20°	120947
25°	103452
30°	85292
35°	56169
40°	30192
45°	13366
50°	5424
55°	3909
60°	2489
65°	1777
70°	1459
75°	974
80°	1452
85°	0



TEST NUMBER: P205083
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L927 F6LC-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.8	11.5
10°-20°	684.0	27.5
20°-30°	783.5	31.5
30°-40°	526.5	21.2
40°-50°	150.4	6.0
50°-60°	36.8	1.5
60°-70°	14.0	0.6
70°-80°	5.5	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1754.3	70.5
0°-40°	2280.7	91.7
0°-60°	2468.0	99.2
0°-90°	2488.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2488.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3189	
5°	3099	287
15°	2454	684
25°	1710	784
35°	839	526
45°	172	150
55°	41	37
65°	14	14
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P205083
CATALOG NUMBER: MRI-DRV-FLD6C-40-L927 F6LC-N-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3189.4
2.5°	3166.7
5°	3098.6
7.5°	2976.0
10°	2826.4
12.5°	2635.8
15°	2454.4
17.5°	2263.9
20°	2073.2
22.5°	1891.8
25°	1710.3
27.5°	1542.5
30°	1347.4
32.5°	1088.8
35°	839.3
37.5°	612.4
40°	421.9
42.5°	276.7
45°	172.4
47.5°	104.3
50°	63.6
52.5°	49.9
55°	40.9
57.5°	31.8
60°	22.7
62.5°	18.1
65°	13.7
67.5°	9.1
70°	9.1
72.5°	4.6
75°	4.6
77.5°	4.6
80°	4.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)