

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P205233

Luminaire Tested: **MRI-DRV-FLD6C-40-L935 F6LC-W-X-LI**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P205233  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD6C-40-L935 F6LC-W-X-LI  
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI  
LEDS, 6LBWLI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4215.0 lumens  
Efficiency: N/A  
Efficacy: 89.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P205233  
CATALOG NUMBER: MRI-DRV-FLD6C-40-L935 F6LC-W-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P205233  
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L935 F6LC-W-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92		
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76		
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69		
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63		
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57		
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52		
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48		
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	144352
5°	145691
10°	149763
15°	153514
20°	155845
25°	152622
30°	143092
35°	127930
40°	103623
45°	68550
50°	34643
55°	14614
60°	4715
65°	1855
70°	1539
75°	1017
80°	0
85°	0



TEST NUMBER: P205233  
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L935 F6LC-W-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	254.0	6.0
10°-20°	763.5	18.1
20°-30°	1151.0	27.3
30°-40°	1178.1	27.9
40°-50°	686.3	16.3
50°-60°	157.7	3.7
60°-70°	19.4	0.5
70°-80°	5.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2168.5	51.4
0°-40°	3346.6	79.4
0°-60°	4190.6	99.4
0°-90°	4215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4215.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2633	
5°	2648	254
15°	2705	764
25°	2523	1151
35°	1912	1178
45°	884	686
55°	153	158
65°	14	19
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P205233  
CATALOG NUMBER: MRI-DRV-FLD6C-40-L935 F6LC-W-X-LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2633.2
2.5°	2628.4
5°	2647.5
7.5°	2666.6
10°	2690.4
12.5°	2695.3
15°	2704.9
17.5°	2695.3
20°	2671.4
22.5°	2594.9
25°	2523.2
27.5°	2408.6
30°	2260.5
32.5°	2107.5
35°	1911.6
37.5°	1691.7
40°	1448.0
42.5°	1175.6
45°	884.2
47.5°	616.4
50°	406.2
52.5°	258.1
55°	152.9
57.5°	81.3
60°	43.0
62.5°	23.9
65°	14.3
67.5°	14.3
70°	9.6
72.5°	4.8
75°	4.8
77.5°	4.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)