

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P485856

Luminaire Tested: **ORLG-24-2-INS-A125-LD4-1LO-27-120-EDD-90**

Issue Date: 3/1/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P485856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35355)
Test Lab: INNOVATION CENTER
Issue Date: 3/1/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: ORLG-24-2-INS-A125-LD4-1LO-27-120-EDD-90
Description: 2X2 ORL LED LUMINAIRE WITH A125 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1022.1 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.21 / 1.32
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P485856

CATALOG NUMBER: ORLG-24-2-INS-A125-LD4-1LO-27-120-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P485856

CATALOG NUMBER: ORLG-24-2-INS-A125-LD4-1LO-27-120-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85		
2	100	92	85	79	97	90	84	79	86	81	77	83	79	75	80	76	73	71		
3	91	81	73	66	89	79	72	66	76	70	65	73	68	64	71	66	62	60		
4	83	72	63	57	81	70	62	56	68	61	55	66	59	55	63	58	54	52		
5	77	64	55	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45		
6	71	58	49	43	69	57	49	43	55	48	42	53	47	42	52	46	41	39		
7	66	53	44	38	64	52	44	38	50	43	37	49	42	37	47	41	37	35		
8	61	48	40	34	60	47	39	34	46	39	34	45	38	33	44	38	33	31		
9	57	44	36	31	56	44	36	30	42	35	30	41	35	30	40	34	30	28		
10	54	41	33	28	53	40	33	28	39	32	28	38	32	27	37	32	27	26		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1071	1071	1071
5°	1071	1063	1065
10°	1056	1052	1053
15°	1038	1036	1037
20°	1017	1025	1025
25°	993	1012	1015
30°	969	997	1005
35°	945	976	980
40°	913	954	953
45°	879	921	930
50°	846	890	902
55°	810	859	864
60°	776	828	822
65°	735	777	762
70°	678	714	681
75°	600	624	545
80°	482	488	381
85°	315	303	222



TEST NUMBER: P485856

CATALOG NUMBER: ORLG-24-2-INS-A125-LD4-1LO-27-120-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.4	3.7
10°-20°	105.2	10.3
20°-30°	156.6	15.3
30°-40°	184.3	18.0
40°-50°	184.8	18.1
50°-60°	162.1	15.9
60°-70°	118.5	11.6
70°-80°	61.1	6.0
80°-90°	12.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	299.1	29.3
0°-40°	483.5	47.3
0°-60°	830.3	81.2
0°-90°	1022.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1022.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	396	394	394	396	394	38
15°	372	373	372	374	372	105
25°	334	336	341	346	342	154
35°	288	289	297	300	298	179
45°	231	232	242	245	244	178
55°	173	177	183	186	184	155
65°	116	118	122	122	120	114
75°	58	58	60	56	52	61
85°	10	10	10	8	7	13
90°	0	0	0	0	0	



TEST NUMBER: P485856

CATALOG NUMBER: ORLG-24-2-INS-A125-LD4-1LO-27-120-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	397.9	397.9	397.9	397.9	397.9
2.5°	399.9	397.9	395.3	397.5	397.1
5°	396.4	393.8	393.6	396.2	394.2
7.5°	392.1	391.6	389.0	391.8	390.7
10°	386.4	386.0	385.1	387.0	385.5
12.5°	379.7	379.2	379.7	380.7	379.7
15°	372.5	373.1	372.0	374.4	372.3
17.5°	362.9	363.6	365.7	366.6	366.4
20°	355.1	355.5	358.1	361.6	357.9
22.5°	344.8	345.9	347.2	353.5	352.7
25°	334.4	335.9	340.9	345.7	342.0
27.5°	323.5	325.0	331.1	334.6	334.2
30°	311.8	313.3	320.9	325.7	323.5
32.5°	299.6	302.2	310.5	314.6	310.5
35°	287.6	288.9	297.0	300.2	298.3
37.5°	271.7	276.7	284.8	287.0	283.5
40°	259.8	260.0	271.5	271.5	271.3
42.5°	244.3	247.8	255.4	259.6	257.4
45°	231.1	232.1	241.9	245.0	244.3
47.5°	216.5	220.8	228.0	231.5	229.7
50°	202.1	205.2	212.6	217.1	215.4
52.5°	188.8	191.2	198.9	201.5	199.7
55°	172.7	176.7	183.0	185.6	184.1
57.5°	158.8	161.7	169.5	170.4	169.5
60°	144.2	147.5	153.8	154.5	152.7
62.5°	130.3	132.5	138.2	138.4	136.4
65°	115.5	118.1	122.1	121.6	119.7
67.5°	101.0	102.7	106.4	104.9	102.7
70°	86.2	87.7	90.7	88.5	86.6
72.5°	71.8	72.9	75.5	72.2	69.8
75°	57.7	58.1	60.0	55.9	52.4
77.5°	43.7	44.2	45.3	41.1	37.2
80°	31.1	31.1	31.5	27.2	24.6
82.5°	19.6	19.6	19.4	16.1	14.6
85°	10.2	10.0	9.8	7.8	7.2
87.5°	3.7	3.7	3.0	2.8	3.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)