

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P308312

Luminaire Tested: **22FCZ2-44HE-UNV-L82765-HRP-CP187-W2A-U-2700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P308312
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-22)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 22FCZ2-44HE-UNV-L82765-HRP-CP187-W2A-U-2700K
Description: 2'X2' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.187" POLYCARB SHEET
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2654.0 lumens
Efficiency: N/A
Efficacy: 71.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 37.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P308312

CATALOG NUMBER: 22FCZ2-44HE-UNV-L82765-HRP-CP187-W2A-U-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P308312

CATALOG NUMBER: 22FCZ2-44HE-UNV-L82765-HRP-CP187-W2A-U-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	87	84	82
2	98	89	82	76	95	87	80	75	84	78	73	80	75	71	77	73	70	68
3	89	78	69	62	86	76	68	62	73	66	61	70	64	60	68	63	59	56
4	81	69	59	52	79	67	59	52	65	57	51	62	56	51	60	55	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	39	50	43	38	49	43	38	36
7	64	50	41	34	62	49	40	34	47	40	34	46	39	34	44	38	33	31
8	59	45	37	31	58	45	36	31	43	36	30	42	35	30	41	35	30	28
9	55	42	33	28	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2352	2352	2352
5°	2343	2361	2356
10°	2338	2351	2361
15°	2318	2341	2355
20°	2296	2330	2354
25°	2272	2311	2351
30°	2242	2305	2351
35°	2200	2277	2349
40°	2153	2258	2370
45°	2103	2236	2408
50°	2033	2229	2474
55°	1940	2246	2569
60°	1829	2280	2694
65°	1727	2324	2878
70°	1475	2424	3083
75°	1236	2524	3203
80°	1012	2439	2672
85°	880	1809	1964



TEST NUMBER: P308312

CATALOG NUMBER: 22FCZ2-44HE-UNV-L82765-HRP-CP187-W2A-U-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.8	3.1
10°-20°	236.9	8.9
20°-30°	359.1	13.5
30°-40°	433.6	16.3
40°-50°	455.6	17.2
50°-60°	428.7	16.2
60°-70°	357.4	13.5
70°-80°	236.8	8.9
80°-90°	63.1	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	678.8	25.6
0°-40°	1112.4	41.9
0°-60°	1996.6	75.2
0°-90°	2654.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2654.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	874	874	874	874	874	
5°	867	869	874	874	872	82
15°	832	835	840	844	846	235
25°	765	770	778	788	792	352
35°	670	676	693	708	715	419
45°	552	561	588	618	633	426
55°	414	432	479	527	548	370
65°	271	295	365	425	452	264
75°	119	166	243	293	308	129
85°	28	44	59	64	64	33
90°	0	0	0	0	0	



TEST NUMBER: P308312

CATALOG NUMBER: 22FCZ2-44HE-UNV-L82765-HRP-CP187-W2A-U-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	873.9	873.9	873.9	873.9	873.9
2.5°	870.6	872.3	875.6	875.6	873.9
5°	867.2	868.9	873.9	873.9	872.3
7.5°	862.2	863.9	867.2	870.6	868.9
10°	855.5	857.2	860.5	863.9	863.9
12.5°	843.8	845.5	852.2	853.8	853.8
15°	832.1	835.4	840.4	843.8	845.5
17.5°	817.0	820.4	827.1	833.8	833.8
20°	801.9	805.3	813.7	820.4	822.0
22.5°	783.5	788.5	796.9	805.3	808.6
25°	765.1	770.1	778.5	788.5	791.9
27.5°	743.3	748.4	760.1	771.8	773.5
30°	721.6	726.6	741.7	751.7	756.7
32.5°	694.8	701.5	716.6	731.6	736.6
35°	669.7	676.4	693.1	708.2	714.9
37.5°	642.9	649.6	668.0	686.4	694.8
40°	612.8	621.1	642.9	663.0	674.7
42.5°	584.3	592.7	614.4	641.2	652.9
45°	552.5	560.9	587.6	617.8	632.8
47.5°	519.0	529.0	560.9	597.7	612.8
50°	485.5	497.2	532.4	574.3	591.0
52.5°	450.4	465.4	505.6	550.8	570.9
55°	413.5	431.9	478.8	527.4	547.5
57.5°	378.4	395.1	450.4	502.3	524.0
60°	339.9	361.6	423.6	477.1	500.6
62.5°	303.0	326.5	395.1	452.0	477.1
65°	271.2	294.7	365.0	425.2	452.0
67.5°	229.4	261.2	339.9	396.8	423.6
70°	187.5	231.0	308.1	366.6	391.8
72.5°	155.7	197.6	276.2	334.8	358.3
75°	118.9	165.7	242.8	293.0	308.1
77.5°	88.7	137.3	207.6	232.7	234.4
80°	65.3	105.5	157.4	165.7	172.4
82.5°	45.2	73.7	102.1	112.2	115.5
85°	28.5	43.5	58.6	63.6	63.6
87.5°	15.1	16.7	20.1	20.1	20.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)