

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: 766608

Luminaire Tested: **HPJC-150xxxx**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: 766608
Test Lab:
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: HPJC-150xxxx
Description: FAIL-SAFE GARAGE LIGHT
Light Source: #003 - 150W HPS CL BU MED 16000 LUMENS
Ballast/Driver: -

| Luminaire Equipment: | <u>Sample No.</u> | <u>Condition</u> | <u>Description</u> |
|----------------------|-------------------|------------------|---------------------------|
| | AS-5443-1 | Good | WHITE TWIN R-EVOLVE FLOOD |
| | AS-5443-2 | Good | REFLECTOR |
| | AS-5443-3 | Good | DRIVER |
| | AS-5443-4 | Good | UPPER MODULE |
| | AS-5443-5 | Good | LENS |
| | AS-5443-6 | Good | DRIVER 2 |
| | AS-5443-7 | Good | TRIM RING |


Summary

Lumens per Lamp: 16000 (1 lamp)
Luminaire Lumens: 13516.2 lumens
Efficiency: 84.5%
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.71 / 1.67 / 3.05
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Semi-Direct

Input Watts (W): 150
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): 7.0
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: 766608
CATALOG NUMBER: HPJC-150xxxx

Luminous Intensity Polar Plot





TEST NUMBER: 766608

CATALOG NUMBER: HPJC-150xxxx

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 93 | 93 | 93 | 93 | 88 | 88 | 88 | 88 | 77 | 77 | 77 | 67 | 67 | 67 | 58 | 58 | 58 | 54 |
| 1 | 79 | 73 | 67 | 62 | 74 | 68 | 63 | 58 | 59 | 55 | 51 | 50 | 47 | 44 | 42 | 40 | 37 | 33 |
| 2 | 70 | 60 | 53 | 46 | 64 | 56 | 49 | 43 | 48 | 42 | 37 | 40 | 36 | 32 | 33 | 30 | 27 | 23 |
| 3 | 62 | 51 | 43 | 36 | 57 | 47 | 40 | 33 | 40 | 34 | 29 | 34 | 29 | 25 | 28 | 24 | 20 | 17 |
| 4 | 56 | 44 | 35 | 29 | 52 | 41 | 33 | 27 | 35 | 28 | 23 | 29 | 24 | 20 | 24 | 20 | 16 | 13 |
| 5 | 51 | 39 | 30 | 24 | 47 | 36 | 28 | 22 | 31 | 24 | 19 | 26 | 20 | 16 | 21 | 17 | 13 | 10 |
| 6 | 47 | 34 | 26 | 20 | 43 | 32 | 24 | 19 | 27 | 21 | 16 | 23 | 18 | 14 | 19 | 14 | 11 | 9 |
| 7 | 43 | 31 | 23 | 17 | 40 | 29 | 21 | 16 | 25 | 18 | 14 | 21 | 15 | 12 | 17 | 13 | 9 | 7 |
| 8 | 40 | 28 | 20 | 15 | 37 | 26 | 19 | 14 | 22 | 16 | 12 | 19 | 14 | 10 | 16 | 11 | 8 | 6 |
| 9 | 37 | 25 | 18 | 13 | 34 | 24 | 17 | 12 | 20 | 15 | 11 | 17 | 12 | 9 | 14 | 10 | 7 | 5 |
| 10 | 35 | 23 | 16 | 12 | 32 | 22 | 15 | 11 | 19 | 13 | 9 | 16 | 11 | 8 | 13 | 9 | 7 | 5 |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 90° | 180° |
|-----|--|-----|------|
| 0° | Luminaire represents a point source (luminous area is zero). | | |
| 5° | No luminance values can be calculated. | | |
| 10° | | | |
| 15° | | | |
| 20° | | | |
| 25° | | | |
| 30° | | | |
| 35° | | | |
| 40° | | | |
| 45° | | | |
| 50° | | | |
| 55° | | | |
| 60° | | | |
| 65° | | | |
| 70° | | | |
| 75° | | | |
| 80° | | | |
| 85° | | | |



TEST NUMBER: 766608
 CATALOG NUMBER: HPJC-150xxxx

ZONAL LUMENS:

CANDELA DISTRIBUTION:

| Zone | Lumens | % Fixture | % Lamp | | 0° | 45° | 90° | 135° | 180° | Flux |
|-----------|---------|-----------|--------|------|------|------|------|------|------|------|
| 0°-10° | 82.6 | 0.6 | 0.5 | 0° | 800 | 800 | 800 | 800 | 800 | |
| 10°-20° | 258.5 | 1.9 | 1.6 | 5° | 779 | 848 | 956 | 848 | 779 | 77 |
| 20°-30° | 430.8 | 3.2 | 2.7 | 15° | 916 | 931 | 902 | 931 | 916 | 254 |
| 30°-40° | 582.3 | 4.3 | 3.6 | 25° | 969 | 978 | 922 | 978 | 969 | 433 |
| 40°-50° | 763.9 | 5.7 | 4.8 | 35° | 886 | 948 | 872 | 948 | 886 | 577 |
| 50°-60° | 1076.7 | 8.0 | 6.7 | 45° | 930 | 1029 | 895 | 1029 | 930 | 752 |
| 60°-70° | 1681.0 | 12.4 | 10.5 | 55° | 1117 | 1357 | 1045 | 1357 | 1117 | 999 |
| 70°-80° | 1981.9 | 14.7 | 12.4 | 65° | 1098 | 2862 | 988 | 2862 | 1098 | 1087 |
| 80°-90° | 1766.8 | 13.1 | 11.0 | 75° | 779 | 4081 | 678 | 4081 | 779 | 823 |
| 90°-100° | 1629.5 | 12.1 | 10.2 | 85° | 447 | 3231 | 374 | 3231 | 447 | 389 |
| 100°-110° | 1516.1 | 11.2 | 9.5 | 90° | 357 | 2964 | 313 | 2964 | 357 | 199 |
| 110°-120° | 1084.1 | 8.0 | 6.8 | 95° | 324 | 2849 | 292 | 2849 | 324 | 271 |
| 120°-130° | 465.3 | 3.4 | 2.9 | 105° | 324 | 2966 | 299 | 2966 | 324 | 349 |
| 130°-140° | 124.5 | 0.9 | 0.8 | 115° | 348 | 2650 | 316 | 2650 | 348 | 296 |
| 140°-150° | 42.5 | 0.3 | 0.3 | 125° | 173 | 792 | 173 | 792 | 173 | 177 |
| 150°-160° | 16.2 | 0.1 | 0.1 | 135° | 93 | 167 | 90 | 167 | 93 | 82 |
| 160°-170° | 6.9 | 0.1 | 0.0 | 145° | 67 | 72 | 65 | 72 | 67 | 41 |
| 170°-180° | 1.2 | 0.0 | 0.0 | 155° | 32 | 24 | 32 | 24 | 32 | 18 |
| 0°-30° | 771.9 | 5.7 | 4.8 | 165° | 24 | 18 | 24 | 18 | 24 | 8 |
| 0°-40° | 1354.2 | 10.0 | 8.5 | 175° | 35 | 23 | 33 | 23 | 35 | 1 |
| 0°-60° | 3194.7 | 23.6 | 20.0 | 180° | 0 | 0 | 0 | 0 | 0 | |
| 0°-90° | 8624.4 | 63.8 | 53.9 | | | | | | | |
| 90°-120° | 4229.8 | 31.3 | 26.4 | | | | | | | |
| 90°-150° | 4862.1 | 36.0 | 30.4 | | | | | | | |
| 90°-180° | 4886.0 | 36.1 | 30.5 | | | | | | | |
| 0°-180° | 13516.2 | 100.0 | 84.5 | | | | | | | |



TEST NUMBER: 766608
 CATALOG NUMBER: HPJC-150xxxx

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|------|------|------|------|------|------|------|------|------|------|------|
| 0° | 800 | 800 | 800 | 800 | 800 | 800 | 800 | 800 | 800 | 800 | 800 |
| 5° | 779 | 778 | 775 | 785 | 810 | 848 | 891 | 943 | 967 | 988 | 956 |
| 15° | 916 | 909 | 910 | 915 | 924 | 931 | 921 | 915 | 902 | 899 | 902 |
| 25° | 969 | 964 | 961 | 972 | 965 | 978 | 956 | 945 | 930 | 918 | 922 |
| 35° | 886 | 882 | 896 | 905 | 918 | 948 | 905 | 889 | 884 | 864 | 872 |
| 45° | 930 | 931 | 938 | 958 | 1006 | 1029 | 988 | 930 | 907 | 905 | 895 |
| 50° | 1033 | 1013 | 1022 | 1050 | 1127 | 1159 | 1092 | 1002 | 967 | 977 | 974 |
| 55° | 1117 | 1118 | 1149 | 1172 | 1245 | 1357 | 1228 | 1117 | 1070 | 1053 | 1045 |
| 60° | 1183 | 1237 | 1314 | 1480 | 1666 | 1825 | 1562 | 1367 | 1136 | 1120 | 1056 |
| 62.5° | 1153 | 1262 | 1327 | 1650 | 2023 | 2315 | 1825 | 1521 | 1118 | 1137 | 1032 |
| 65° | 1098 | 1255 | 1293 | 1783 | 2339 | 2862 | 2083 | 1676 | 1079 | 1136 | 988 |
| 67.5° | 1053 | 1230 | 1258 | 1872 | 2605 | 3347 | 2253 | 1795 | 1024 | 1130 | 943 |
| 70° | 980 | 1175 | 1191 | 1920 | 2838 | 3718 | 2422 | 1862 | 956 | 1094 | 867 |
| 72.5° | 886 | 1095 | 1104 | 1919 | 3007 | 3964 | 2545 | 1869 | 907 | 1034 | 775 |
| 75° | 779 | 1000 | 1009 | 1880 | 3077 | 4081 | 2615 | 1825 | 835 | 949 | 678 |
| 77.5° | 672 | 900 | 919 | 1811 | 3065 | 3964 | 2635 | 1757 | 763 | 862 | 586 |
| 80° | 579 | 809 | 840 | 1737 | 3045 | 3706 | 2620 | 1703 | 688 | 782 | 506 |
| 82.5° | 495 | 719 | 775 | 1656 | 3020 | 3452 | 2602 | 1636 | 622 | 704 | 431 |
| 85° | 447 | 639 | 737 | 1576 | 3018 | 3231 | 2609 | 1562 | 574 | 633 | 374 |
| 87.5° | 397 | 571 | 716 | 1512 | 3034 | 3080 | 2597 | 1497 | 558 | 572 | 339 |
| 90° | 357 | 520 | 713 | 1451 | 3054 | 2964 | 2574 | 1430 | 561 | 504 | 313 |
| 95° | 324 | 435 | 768 | 1365 | 3096 | 2849 | 2557 | 1314 | 624 | 393 | 292 |
| 105° | 324 | 358 | 976 | 1263 | 2963 | 2966 | 2646 | 1104 | 844 | 321 | 299 |
| 115° | 348 | 387 | 904 | 1026 | 2210 | 2650 | 2163 | 849 | 862 | 359 | 316 |
| 125° | 173 | 193 | 226 | 286 | 512 | 792 | 467 | 257 | 210 | 176 | 173 |
| 135° | 93 | 94 | 98 | 115 | 139 | 167 | 139 | 114 | 97 | 93 | 90 |
| 145° | 67 | 65 | 63 | 59 | 59 | 72 | 58 | 61 | 63 | 65 | 65 |
| 155° | 32 | 31 | 30 | 27 | 24 | 24 | 26 | 27 | 31 | 32 | 32 |
| 165° | 24 | 23 | 22 | 19 | 17 | 18 | 19 | 21 | 23 | 24 | 24 |
| 175° | 35 | 33 | 30 | 26 | 23 | 23 | 23 | 26 | 30 | 34 | 33 |
| 180° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |



TEST NUMBER: 766608
 CATALOG NUMBER: HPJC-150xxxx

CANDELA DISTRIBUTION (continued):

| | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|------|------|------|------|------|------|------|------|------|------|
| 0° | 800 | 800 | 800 | 800 | 800 | 800 | 800 | 800 | 800 | 800 |
| 5° | 988 | 967 | 943 | 891 | 848 | 810 | 785 | 775 | 778 | 779 |
| 15° | 899 | 902 | 915 | 921 | 931 | 924 | 915 | 910 | 909 | 916 |
| 25° | 918 | 930 | 945 | 956 | 978 | 965 | 972 | 961 | 964 | 969 |
| 35° | 864 | 884 | 889 | 905 | 948 | 918 | 905 | 896 | 882 | 886 |
| 45° | 905 | 907 | 930 | 988 | 1029 | 1006 | 958 | 938 | 931 | 930 |
| 50° | 977 | 967 | 1002 | 1092 | 1159 | 1127 | 1050 | 1022 | 1013 | 1033 |
| 55° | 1053 | 1070 | 1117 | 1228 | 1357 | 1245 | 1172 | 1149 | 1118 | 1117 |
| 60° | 1120 | 1136 | 1367 | 1562 | 1825 | 1666 | 1480 | 1314 | 1237 | 1183 |
| 62.5° | 1137 | 1118 | 1521 | 1825 | 2315 | 2023 | 1650 | 1327 | 1262 | 1153 |
| 65° | 1136 | 1079 | 1676 | 2083 | 2862 | 2339 | 1783 | 1293 | 1255 | 1098 |
| 67.5° | 1130 | 1024 | 1795 | 2253 | 3347 | 2605 | 1872 | 1258 | 1230 | 1053 |
| 70° | 1094 | 956 | 1862 | 2422 | 3718 | 2838 | 1920 | 1191 | 1175 | 980 |
| 72.5° | 1034 | 907 | 1869 | 2545 | 3964 | 3007 | 1919 | 1104 | 1095 | 886 |
| 75° | 949 | 835 | 1825 | 2615 | 4081 | 3077 | 1880 | 1009 | 1000 | 779 |
| 77.5° | 862 | 763 | 1757 | 2635 | 3964 | 3065 | 1811 | 919 | 900 | 672 |
| 80° | 782 | 688 | 1703 | 2620 | 3706 | 3045 | 1737 | 840 | 809 | 579 |
| 82.5° | 704 | 622 | 1636 | 2602 | 3452 | 3020 | 1656 | 775 | 719 | 495 |
| 85° | 633 | 574 | 1562 | 2609 | 3231 | 3018 | 1576 | 737 | 639 | 447 |
| 87.5° | 572 | 558 | 1497 | 2597 | 3080 | 3034 | 1512 | 716 | 571 | 397 |
| 90° | 504 | 561 | 1430 | 2574 | 2964 | 3054 | 1451 | 713 | 520 | 357 |
| 95° | 393 | 624 | 1314 | 2557 | 2849 | 3096 | 1365 | 768 | 435 | 324 |
| 105° | 321 | 844 | 1104 | 2646 | 2966 | 2963 | 1263 | 976 | 358 | 324 |
| 115° | 359 | 862 | 849 | 2163 | 2650 | 2210 | 1026 | 904 | 387 | 348 |
| 125° | 176 | 210 | 257 | 467 | 792 | 512 | 286 | 226 | 193 | 173 |
| 135° | 93 | 97 | 114 | 139 | 167 | 139 | 115 | 98 | 94 | 93 |
| 145° | 65 | 63 | 61 | 58 | 72 | 59 | 59 | 63 | 65 | 67 |
| 155° | 32 | 31 | 27 | 26 | 24 | 24 | 27 | 30 | 31 | 32 |
| 165° | 24 | 23 | 21 | 19 | 18 | 17 | 19 | 22 | 23 | 24 |
| 175° | 34 | 30 | 26 | 23 | 23 | 23 | 26 | 30 | 33 | 35 |
| 180° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |

(END OF REPORT)