

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P308391

Luminaire Tested: **22FCZ2-24HE-UNV-L82765-RDP-CA125-W2A-U-5700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P308391  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-24)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 22FCZ2-24HE-UNV-L82765-RDP-CA125-W2A-U-5700K  
Description: 2'X2' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" ACRYLIC SHEET  
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1526.0 lumens  
Efficiency: N/A  
Efficacy: 78.7 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.3 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P308391

CATALOG NUMBER: 22FCZ2-24HE-UNV-L82765-RDP-CA125-W2A-U-5700K

### Luminous Intensity Polar Plot





TEST NUMBER: P308391

CATALOG NUMBER: 22FCZ2-24HE-UNV-L82765-RDP-CA125-W2A-U-5700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	86	88	86	84	82
2	97	88	81	75	95	86	80	74	83	77	72	80	75	71	76	72	69	67
3	88	77	68	61	86	75	67	61	72	65	60	70	64	59	67	62	58	55
4	80	68	59	51	78	66	58	51	64	56	50	61	55	50	59	54	49	47
5	74	60	51	44	72	59	50	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	44	38	51	43	38	50	43	37	48	42	37	35
7	63	49	40	33	61	48	39	33	47	39	33	45	38	33	44	37	33	31
8	59	45	36	30	57	44	35	30	43	35	29	41	34	29	40	34	29	27
9	55	41	32	27	53	40	32	27	39	32	26	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1290	1290	1290
5°	1283	1292	1292
10°	1279	1288	1294
15°	1273	1285	1295
20°	1263	1283	1296
25°	1260	1287	1300
30°	1249	1277	1301
35°	1236	1272	1309
40°	1219	1270	1325
45°	1200	1269	1367
50°	1175	1278	1424
55°	1143	1306	1506
60°	1105	1341	1613
65°	1030	1408	1744
70°	945	1475	1908
75°	829	1552	1972
80°	713	1478	1548
85°	624	1074	1179



TEST NUMBER: P308391

CATALOG NUMBER: 22FCZ2-24HE-UNV-L82765-RDP-CA125-W2A-U-5700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.3	3.0
10°-20°	130.2	8.5
20°-30°	198.6	13.0
30°-40°	242.5	15.9
40°-50°	259.3	17.0
50°-60°	250.3	16.4
60°-70°	215.5	14.1
70°-80°	145.8	9.6
80°-90°	38.5	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	374.2	24.5
0°-40°	616.7	40.4
0°-60°	1126.3	73.8
0°-90°	1526.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1526.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	479	479	479	479	479	
5°	475	476	478	478	478	45
15°	457	458	461	464	465	129
25°	424	427	433	436	438	195
35°	376	379	387	395	398	235
45°	315	321	333	350	359	243
55°	244	252	278	306	321	218
65°	162	177	221	256	274	161
75°	80	106	149	180	190	85
85°	20	28	35	36	38	23
90°	0	0	0	0	0	



TEST NUMBER: P308391

CATALOG NUMBER: 22FC22-24HE-UNV-L82765-RDP-CA125-W2A-U-5700K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	479.3	479.3	479.3	479.3	479.3
2.5°	476.0	477.1	479.3	479.3	480.5
5°	474.9	476.0	478.2	478.2	478.2
7.5°	471.5	472.6	474.9	476.0	476.0
10°	468.1	469.2	471.5	472.6	473.7
12.5°	462.5	463.6	467.0	469.2	469.2
15°	456.9	458.0	461.4	463.6	464.7
17.5°	450.2	452.4	455.8	458.0	459.1
20°	441.2	443.4	447.9	451.3	452.4
22.5°	433.3	435.6	440.1	443.4	445.7
25°	424.3	426.6	433.3	435.6	437.8
27.5°	413.1	415.4	421.0	425.5	428.8
30°	401.9	404.1	410.9	416.5	418.7
32.5°	389.5	392.9	400.8	405.3	408.6
35°	376.1	379.4	387.3	395.1	398.5
37.5°	362.6	366.0	373.8	383.9	388.4
40°	346.9	351.4	361.5	374.9	377.2
42.5°	332.3	337.9	346.9	362.6	368.2
45°	315.4	321.1	333.4	350.2	359.2
47.5°	299.7	305.3	318.8	339.0	350.2
50°	280.6	288.5	305.3	328.9	340.1
52.5°	262.7	269.4	291.9	317.7	331.2
55°	243.6	251.5	278.4	306.5	321.1
57.5°	226.8	233.5	263.8	295.2	312.1
60°	205.4	214.4	249.2	282.9	299.7
62.5°	183.0	196.5	234.6	269.4	287.4
65°	161.7	177.4	221.1	255.9	273.9
67.5°	142.6	159.4	204.3	241.4	258.2
70°	120.1	141.4	187.5	223.4	242.5
72.5°	99.9	123.5	168.4	204.3	221.1
75°	79.7	105.5	149.3	179.6	189.7
77.5°	61.7	86.4	128.0	137.0	138.1
80°	46.0	68.5	95.4	96.5	99.9
82.5°	31.4	48.3	61.7	67.4	68.5
85°	20.2	28.1	34.8	35.9	38.2
87.5°	9.0	10.1	12.3	11.2	11.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)