

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P308897

Luminaire Tested: **22FCZ2-20HE-UNV-L82765-S-CP187-W2A-U-2700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P308897  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-23)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 22FCZ2-20HE-UNV-L82765-S-CP187-W2A-U-2700K  
Description: 2'X2' TROFFER LED MODULE, SMOOTH LENS, 0.187" POLYCARB SHEET  
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1762.0 lumens  
Efficiency: N/A  
Efficacy: 105.5 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.26 / 1.34  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 16.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P308897

CATALOG NUMBER: 22FCZ2-20HE-UNV-L82765-S-CP187-W2A-U-2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P308897

CATALOG NUMBER: 22FC22-20HE-UNV-L82765-S-CP187-W2A-U-2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	94	97	94	91	93	90	88	89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	90	79	71	64	87	77	70	63	74	68	62	72	66	61	69	64	60	58
4	82	70	61	54	80	69	60	54	66	59	53	64	57	52	61	56	52	49
5	75	62	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	43
6	70	56	47	41	68	55	47	41	53	46	40	52	45	40	50	44	39	37
7	65	51	42	36	63	50	42	36	49	41	36	47	40	35	46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	31	30
9	56	43	35	29	55	42	34	29	41	34	29	40	33	29	39	33	28	27
10	53	40	32	26	51	39	31	26	38	31	26	37	31	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1699	1699	1699
5°	1688	1701	1706
10°	1678	1694	1703
15°	1656	1679	1695
20°	1629	1662	1688
25°	1597	1645	1677
30°	1556	1612	1663
35°	1512	1583	1647
40°	1461	1551	1632
45°	1408	1514	1614
50°	1356	1473	1600
55°	1292	1446	1589
60°	1235	1412	1584
65°	1152	1403	1602
70°	1061	1391	1649
75°	958	1410	1735
80°	828	1452	1630
85°	685	1220	1220



TEST NUMBER: P308897

CATALOG NUMBER: 22FCZ2-20HE-UNV-L82765-S-CP187-W2A-U-2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.7	3.4
10°-20°	169.9	9.6
20°-30°	254.2	14.4
30°-40°	301.1	17.1
40°-50°	306.9	17.4
50°-60°	275.0	15.6
60°-70°	215.3	12.2
70°-80°	138.8	7.9
80°-90°	41.0	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	483.9	27.5
0°-40°	785.0	44.5
0°-60°	1366.8	77.6
0°-90°	1762.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1762.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	631	631	631	631	631	
5°	625	626	630	631	631	59
15°	594	598	603	608	608	168
25°	538	543	554	562	565	248
35°	460	466	482	497	502	288
45°	370	378	398	418	424	286
55°	275	284	308	330	339	247
65°	181	192	220	242	252	180
75°	92	106	136	159	167	99
85°	22	30	40	40	40	26
90°	0	0	0	0	0	



TEST NUMBER: P308897

CATALOG NUMBER: 22FCZ2-20HE-UNV-L82765-S-CP187-W2A-U-2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	631.4	631.4	631.4	631.4	631.4
2.5°	627.3	628.9	632.2	633.0	633.0
5°	624.8	626.4	629.7	630.6	631.4
7.5°	620.7	621.5	625.6	627.3	628.1
10°	614.1	615.8	619.9	622.3	623.2
12.5°	605.1	607.5	612.5	615.8	616.6
15°	594.4	597.7	602.6	607.5	608.4
17.5°	582.9	586.2	592.7	598.5	600.1
20°	568.9	573.0	580.4	587.0	589.5
22.5°	554.9	558.2	567.3	575.5	577.9
25°	537.7	542.6	554.1	561.5	564.8
27.5°	519.6	525.3	536.8	546.7	550.0
30°	500.7	506.4	518.8	531.1	535.2
32.5°	480.9	487.5	502.3	514.6	518.8
35°	460.4	466.1	481.8	496.6	501.5
37.5°	439.0	443.9	462.0	477.6	482.6
40°	416.0	422.6	441.5	459.6	464.5
42.5°	393.0	400.4	419.3	439.0	443.9
45°	369.9	378.2	397.9	418.5	424.2
47.5°	347.8	354.3	376.5	396.3	404.5
50°	323.9	330.5	351.9	374.1	382.3
52.5°	299.2	308.3	331.3	352.7	362.5
55°	275.4	284.4	308.3	329.7	338.7
57.5°	253.2	260.6	285.3	307.5	316.5
60°	229.4	235.9	262.3	286.1	294.3
62.5°	203.9	213.7	240.9	263.1	272.9
65°	180.9	191.6	220.3	241.7	251.6
67.5°	159.5	169.4	197.3	220.3	231.0
70°	134.8	148.0	176.8	199.8	209.6
72.5°	115.1	126.6	156.2	179.2	189.9
75°	92.1	106.1	135.6	158.7	166.9
77.5°	73.2	87.1	115.1	133.2	137.3
80°	53.4	67.4	93.7	102.8	105.2
82.5°	36.2	49.3	67.4	69.9	70.7
85°	22.2	30.4	39.5	39.5	39.5
87.5°	10.7	12.3	14.0	13.2	13.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)