

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309286

Luminaire Tested: **24FCZ2-35-UNV-L82765-HRP-CA125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P309286  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-35-UNV-L82765-HRP-CA125-W2A-U-3500K  
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" ACRYLIC SHEET  
Light Source: (168) 3500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2401.0 lumens  
Efficiency: N/A  
Efficacy: 85.4 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P309286

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-HRP-CA125-W2A-U-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P309286

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-HRP-CA125-W2A-U-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1048	1048	1048
5°	1049	1045	1049
10°	1046	1045	1052
15°	1040	1043	1053
20°	1033	1041	1055
25°	1021	1036	1057
30°	1009	1032	1060
35°	992	1027	1062
40°	975	1020	1072
45°	953	1020	1088
50°	922	1018	1117
55°	889	1026	1158
60°	839	1041	1209
65°	775	1066	1277
70°	676	1103	1360
75°	548	1160	1406
80°	405	1137	1137
85°	310	838	946



TEST NUMBER: P309286

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-HRP-CA125-W2A-U-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.8	3.1
10°-20°	211.9	8.8
20°-30°	322.6	13.4
30°-40°	391.7	16.3
40°-50°	413.9	17.2
50°-60°	390.5	16.3
60°-70°	324.7	13.5
70°-80°	213.6	8.9
80°-90°	58.2	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.3	25.3
0°-40°	1000.1	41.7
0°-60°	1804.4	75.2
0°-90°	2401.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2401.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	779	779	779	779	779	
5°	777	777	774	777	777	74
15°	747	748	749	756	756	211
25°	688	692	698	710	712	317
35°	604	611	625	641	646	378
45°	501	511	536	562	572	385
55°	379	395	437	478	494	338
65°	243	271	335	384	401	240
75°	106	154	223	264	270	114
85°	20	44	54	60	61	25
90°	0	0	0	0	0	



TEST NUMBER: P309286

CATALOG NUMBER: 24FC22-35-UNV-L82765-HRP-CA125-W2A-U-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	779.0	779.0	779.0	779.0	779.0
2.5°	780.0	779.0	775.0	779.0	779.0
5°	777.0	777.0	774.0	777.0	777.0
7.5°	772.0	772.0	770.0	774.0	774.0
10°	765.9	765.9	764.9	770.0	770.0
12.5°	756.9	757.9	756.9	762.9	762.9
15°	746.8	747.8	748.9	755.9	755.9
17.5°	733.8	735.8	737.8	745.8	746.8
20°	721.7	722.7	726.7	735.8	736.8
22.5°	705.6	708.6	713.7	722.7	725.7
25°	687.5	691.6	697.6	709.6	711.7
27.5°	670.4	673.5	681.5	694.6	698.6
30°	649.3	654.4	664.4	677.5	682.5
32.5°	629.2	634.3	646.3	660.4	664.4
35°	604.1	611.1	625.2	641.3	646.3
37.5°	580.0	587.0	604.1	622.2	628.2
40°	554.9	562.9	581.0	602.1	610.1
42.5°	527.7	538.8	558.9	582.0	591.0
45°	500.6	510.6	535.8	561.9	571.9
47.5°	471.4	483.5	510.6	541.8	553.8
50°	440.3	455.3	486.5	520.7	533.7
52.5°	409.1	426.2	461.4	499.6	513.6
55°	378.9	395.0	437.2	478.5	493.5
57.5°	345.8	365.9	412.1	456.3	471.4
60°	311.6	333.7	387.0	433.2	449.3
62.5°	277.4	302.6	362.9	409.1	426.2
65°	243.3	271.4	334.7	384.0	401.1
67.5°	210.1	241.2	308.6	357.8	374.9
70°	171.9	211.1	280.4	328.7	345.8
72.5°	136.7	181.9	253.3	298.5	313.6
75°	105.5	153.8	223.1	264.4	270.4
77.5°	77.4	125.6	192.0	206.1	207.1
80°	52.3	100.5	146.8	144.7	146.8
82.5°	34.2	75.4	92.5	103.5	104.5
85°	20.1	44.2	54.3	60.3	61.3
87.5°	10.1	15.1	19.1	20.1	22.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)