

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309364

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-HRP-CP250-W2A-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P309364  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-40HE-UNV-L82765-HRP-CP250-W2A-U-6500K  
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.250"  
POLYCARB SHEET  
Light Source: (336) 6500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2740.0 lumens  
Efficiency: N/A  
Efficacy: 86.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 31.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P309364

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-HRP-CP250-W2A-U-6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P309364

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-HRP-CP250-W2A-U-6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1196	1196	1196
5°	1198	1193	1198
10°	1194	1193	1201
15°	1187	1190	1202
20°	1179	1187	1204
25°	1165	1182	1206
30°	1151	1178	1210
35°	1132	1172	1212
40°	1112	1165	1223
45°	1087	1163	1242
50°	1052	1162	1275
55°	1015	1171	1321
60°	957	1188	1380
65°	884	1216	1457
70°	772	1259	1552
75°	626	1324	1604
80°	462	1298	1298
85°	354	956	1081



TEST NUMBER: P309364

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-HRP-CP250-W2A-U-6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.2	3.1
10°-20°	241.8	8.8
20°-30°	368.2	13.4
30°-40°	447.0	16.3
40°-50°	472.3	17.2
50°-60°	445.7	16.3
60°-70°	370.6	13.5
70°-80°	243.8	8.9
80°-90°	66.4	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.2	25.3
0°-40°	1141.3	41.7
0°-60°	2059.2	75.2
0°-90°	2740.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2740.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	889	889	889	889	889	
5°	887	887	883	887	887	84
15°	852	853	855	863	863	240
25°	785	789	796	810	812	362
35°	689	697	714	732	738	432
45°	571	583	611	641	653	440
55°	432	451	499	546	563	385
65°	278	310	382	438	458	274
75°	120	176	255	302	309	130
85°	23	50	62	69	70	28
90°	0	0	0	0	0	



TEST NUMBER: P309364

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-HRP-CP250-W2A-U-6500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	889.0	889.0	889.0	889.0	889.0
2.5°	890.1	889.0	884.4	889.0	889.0
5°	886.7	886.7	883.3	886.7	886.7
7.5°	881.0	881.0	878.7	883.3	883.3
10°	874.1	874.1	872.9	878.7	878.7
12.5°	863.8	864.9	863.8	870.6	870.6
15°	852.3	853.4	854.6	862.6	862.6
17.5°	837.4	839.7	842.0	851.1	852.3
20°	823.6	824.8	829.3	839.7	840.8
22.5°	805.3	808.7	814.4	824.8	828.2
25°	784.6	789.2	796.1	809.8	812.1
27.5°	765.1	768.6	777.7	792.6	797.2
30°	741.0	746.8	758.2	773.1	778.9
32.5°	718.1	723.8	737.6	753.6	758.2
35°	689.4	697.4	713.5	731.8	737.6
37.5°	661.9	669.9	689.4	710.0	716.9
40°	633.2	642.4	663.0	687.1	696.3
42.5°	602.2	614.8	637.8	664.2	674.5
45°	571.3	582.7	611.4	641.2	652.7
47.5°	538.0	551.8	582.7	618.3	632.0
50°	502.4	519.6	555.2	594.2	609.1
52.5°	466.9	486.4	526.5	570.1	586.2
55°	432.5	450.8	499.0	546.0	563.2
57.5°	394.6	417.5	470.3	520.8	538.0
60°	355.6	380.8	441.6	494.4	512.7
62.5°	316.6	345.3	414.1	466.9	486.4
65°	277.6	309.7	382.0	438.2	457.7
67.5°	239.7	275.3	352.2	408.4	427.9
70°	196.2	240.9	320.0	375.1	394.6
72.5°	156.0	207.6	289.1	340.7	357.9
75°	120.4	175.5	254.7	301.7	308.6
77.5°	88.3	143.4	219.1	235.2	236.3
80°	59.6	114.7	167.5	165.2	167.5
82.5°	39.0	86.0	105.5	118.2	119.3
85°	22.9	50.5	61.9	68.8	70.0
87.5°	11.5	17.2	21.8	22.9	25.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)