

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309480

Luminaire Tested: **24FCZ2-45-UNV-L82765-HRP-CP125-W2A-U-5700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-45-UNV-L82765-HRP-CP125-W2A-U-5700K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" POLYCARB SHEET
Light Source: (168) 5700K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3202.0 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309480

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-HRP-CP125-W2A-U-5700K

Luminous Intensity Polar Plot





TEST NUMBER: P309480

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-HRP-CP125-W2A-U-5700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1398	1398	1398
5°	1400	1394	1400
10°	1396	1394	1403
15°	1387	1391	1404
20°	1378	1388	1407
25°	1361	1381	1409
30°	1345	1377	1414
35°	1323	1370	1416
40°	1300	1361	1429
45°	1270	1360	1451
50°	1229	1358	1490
55°	1186	1368	1544
60°	1118	1389	1612
65°	1033	1421	1703
70°	902	1471	1814
75°	732	1547	1875
80°	540	1516	1516
85°	414	1118	1263



TEST NUMBER: P309480

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-HRP-CP125-W2A-U-5700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.4	3.1
10°-20°	282.6	8.8
20°-30°	430.2	13.4
30°-40°	522.4	16.3
40°-50°	551.9	17.2
50°-60°	520.8	16.3
60°-70°	433.0	13.5
70°-80°	284.9	8.9
80°-90°	77.7	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	811.3	25.3
0°-40°	1333.7	41.7
0°-60°	2406.4	75.2
0°-90°	3202.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3202.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1039	1039	1039	1039	1039	
5°	1036	1036	1032	1036	1036	98
15°	996	997	999	1008	1008	281
25°	917	922	930	946	949	423
35°	806	815	834	855	862	504
45°	668	681	714	749	763	514
55°	505	527	583	638	658	450
65°	324	362	446	512	535	321
75°	141	205	298	353	361	152
85°	27	59	72	80	82	33
90°	0	0	0	0	0	



TEST NUMBER: P309480

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-HRP-CP125-W2A-U-5700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1038.9	1038.9	1038.9	1038.9	1038.9
2.5°	1040.2	1038.9	1033.5	1038.9	1038.9
5°	1036.2	1036.2	1032.2	1036.2	1036.2
7.5°	1029.5	1029.5	1026.8	1032.2	1032.2
10°	1021.5	1021.5	1020.1	1026.8	1026.8
12.5°	1009.4	1010.7	1009.4	1017.4	1017.4
15°	996.0	997.3	998.7	1008.1	1008.1
17.5°	978.6	981.2	983.9	994.7	996.0
20°	962.5	963.8	969.2	981.2	982.6
22.5°	941.0	945.1	951.8	963.8	967.8
25°	916.9	922.3	930.3	946.4	949.1
27.5°	894.1	898.1	908.9	926.3	931.7
30°	866.0	872.7	886.1	903.5	910.2
32.5°	839.2	845.9	861.9	880.7	886.1
35°	805.6	815.0	833.8	855.2	861.9
37.5°	773.5	782.9	805.6	829.8	837.8
40°	740.0	750.7	774.8	803.0	813.7
42.5°	703.8	718.5	745.3	776.2	788.2
45°	667.6	681.0	714.5	749.3	762.7
47.5°	628.7	644.8	681.0	722.5	738.6
50°	587.1	607.2	648.8	694.4	711.8
52.5°	545.6	568.4	615.3	666.2	685.0
55°	505.4	526.8	583.1	638.1	658.2
57.5°	461.1	487.9	549.6	608.6	628.7
60°	415.6	445.0	516.1	577.8	599.2
62.5°	370.0	403.5	483.9	545.6	568.4
65°	324.4	361.9	446.4	512.1	534.9
67.5°	280.2	321.7	411.5	477.2	500.0
70°	229.2	281.5	374.0	438.3	461.1
72.5°	182.3	242.6	337.8	398.1	418.2
75°	140.8	205.1	297.6	352.6	360.6
77.5°	103.2	167.6	256.0	274.8	276.1
80°	69.7	134.1	195.7	193.0	195.7
82.5°	45.6	100.5	123.3	138.1	139.4
85°	26.8	59.0	72.4	80.4	81.8
87.5°	13.4	20.1	25.5	26.8	29.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)