

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309414

Luminaire Tested: **24FCZ2-45HE-UNV-L82765-HRP-CA08-W2A-U-4500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-45HE-UNV-L82765-HRP-CA08-W2A-U-4500K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.08" ACRYLIC SHEET
Light Source: (336) 4500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3160.0 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 34.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309414

CATALOG NUMBER: 24FCZ2-45HE-UNV-L82765-HRP-CA08-W2A-U-4500K

Luminous Intensity Polar Plot





TEST NUMBER: P309414

CATALOG NUMBER: 24FCZ2-45HE-UNV-L82765-HRP-CA08-W2A-U-4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1380	1380	1380
5°	1381	1376	1381
10°	1377	1375	1385
15°	1369	1373	1386
20°	1360	1370	1388
25°	1343	1363	1390
30°	1328	1359	1396
35°	1306	1352	1397
40°	1283	1343	1410
45°	1254	1342	1432
50°	1213	1340	1470
55°	1170	1350	1524
60°	1104	1371	1591
65°	1019	1402	1680
70°	890	1452	1790
75°	722	1527	1850
80°	533	1496	1496
85°	409	1102	1246



TEST NUMBER: P309414

CATALOG NUMBER: 24FCZ2-45HE-UNV-L82765-HRP-CA08-W2A-U-4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.1	3.1
10°-20°	278.9	8.8
20°-30°	424.6	13.4
30°-40°	515.6	16.3
40°-50°	544.7	17.2
50°-60°	514.0	16.3
60°-70°	427.3	13.5
70°-80°	281.2	8.9
80°-90°	76.6	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	800.6	25.3
0°-40°	1316.2	41.7
0°-60°	2374.9	75.2
0°-90°	3160.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3160.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1025	1025	1025	1025	1025	
5°	1023	1023	1019	1023	1023	97
15°	983	984	986	995	995	277
25°	905	910	918	934	937	417
35°	795	804	823	844	851	498
45°	659	672	705	740	753	507
55°	499	520	576	630	650	444
65°	320	357	440	505	528	316
75°	139	202	294	348	356	150
85°	26	58	71	79	81	32
90°	0	0	0	0	0	



TEST NUMBER: P309414

CATALOG NUMBER: 24FCZ2-45HE-UNV-L82765-HRP-CA08-W2A-U-4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1025.3	1025.3	1025.3	1025.3	1025.3
2.5°	1026.6	1025.3	1020.0	1025.3	1025.3
5°	1022.6	1022.6	1018.6	1022.6	1022.6
7.5°	1016.0	1016.0	1013.4	1018.6	1018.6
10°	1008.1	1008.1	1006.7	1013.4	1013.4
12.5°	996.2	997.5	996.2	1004.1	1004.1
15°	982.9	984.3	985.6	994.8	994.8
17.5°	965.7	968.4	971.0	981.6	982.9
20°	949.9	951.2	956.5	968.4	969.7
22.5°	928.7	932.7	939.3	951.2	955.1
25°	904.9	910.2	918.1	934.0	936.6
27.5°	882.4	886.4	896.9	914.1	919.4
30°	854.6	861.2	874.5	891.6	898.3
32.5°	828.1	834.8	850.6	869.2	874.5
35°	795.1	804.3	822.9	844.0	850.6
37.5°	763.3	772.6	795.1	818.9	826.8
40°	730.3	740.8	764.6	792.4	803.0
42.5°	694.5	709.1	735.5	766.0	777.9
45°	658.8	672.0	705.1	739.5	752.7
47.5°	620.5	636.3	672.0	713.1	728.9
50°	579.4	599.3	640.3	685.3	702.5
52.5°	538.4	560.9	607.2	657.5	676.0
55°	498.7	519.9	575.5	629.7	649.6
57.5°	455.1	481.5	542.4	600.6	620.5
60°	410.1	439.2	509.3	570.2	591.3
62.5°	365.1	398.2	477.6	538.4	560.9
65°	320.1	357.2	440.5	505.4	527.8
67.5°	276.5	317.5	406.1	471.0	493.4
70°	226.2	277.8	369.1	432.6	455.1
72.5°	179.9	239.4	333.4	392.9	412.8
75°	138.9	202.4	293.7	347.9	355.9
77.5°	101.9	165.4	252.7	271.2	272.5
80°	68.8	132.3	193.1	190.5	193.1
82.5°	45.0	99.2	121.7	136.3	137.6
85°	26.5	58.2	71.4	79.4	80.7
87.5°	13.2	19.8	25.1	26.5	29.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)