

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309606

Luminaire Tested: **24FCZ2-55HE-UNV-L82765-HRP-CA125-W2A-U-5700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-55HE-UNV-L82765-HRP-CA125-W2A-U-5700K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 5700K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3999.0 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 44.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309606

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-HRP-CA125-W2A-U-5700K

Luminous Intensity Polar Plot





TEST NUMBER: P309606

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-HRP-CA125-W2A-U-5700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1746	1746	1746
5°	1748	1741	1748
10°	1743	1741	1752
15°	1733	1737	1754
20°	1721	1733	1757
25°	1700	1725	1760
30°	1680	1719	1766
35°	1653	1710	1768
40°	1623	1700	1785
45°	1586	1698	1813
50°	1535	1696	1861
55°	1481	1708	1928
60°	1397	1735	2014
65°	1290	1775	2127
70°	1126	1838	2266
75°	914	1932	2341
80°	675	1894	1894
85°	517	1396	1576



TEST NUMBER: P309606

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-HRP-CA125-W2A-U-5700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.9	3.1
10°-20°	353.0	8.8
20°-30°	537.3	13.4
30°-40°	652.4	16.3
40°-50°	689.3	17.2
50°-60°	650.4	16.3
60°-70°	540.8	13.5
70°-80°	355.8	8.9
80°-90°	97.0	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1013.2	25.3
0°-40°	1665.6	41.7
0°-60°	3005.4	75.2
0°-90°	3999.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3999.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1298	1298	1298	1298	1298	
5°	1294	1294	1289	1294	1294	123
15°	1244	1246	1247	1259	1259	351
25°	1145	1152	1162	1182	1185	528
35°	1006	1018	1041	1068	1076	630
45°	834	850	892	936	953	642
55°	631	658	728	797	822	562
65°	405	452	558	640	668	400
75°	176	256	372	440	450	189
85°	34	74	90	100	102	41
90°	0	0	0	0	0	



TEST NUMBER: P309606

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-HRP-CA125-W2A-U-5700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1297.5	1297.5	1297.5	1297.5	1297.5
2.5°	1299.2	1297.5	1290.8	1297.5	1297.5
5°	1294.1	1294.1	1289.1	1294.1	1294.1
7.5°	1285.8	1285.8	1282.4	1289.1	1289.1
10°	1275.7	1275.7	1274.0	1282.4	1282.4
12.5°	1260.6	1262.3	1260.6	1270.7	1270.7
15°	1243.9	1245.6	1247.3	1259.0	1259.0
17.5°	1222.1	1225.5	1228.8	1242.2	1243.9
20°	1202.1	1203.7	1210.4	1225.5	1227.2
22.5°	1175.3	1180.3	1188.7	1203.7	1208.7
25°	1145.1	1151.8	1161.9	1182.0	1185.3
27.5°	1116.7	1121.7	1135.1	1156.8	1163.5
30°	1081.5	1089.9	1106.6	1128.4	1136.8
32.5°	1048.0	1056.4	1076.5	1099.9	1106.6
35°	1006.2	1017.9	1041.3	1068.1	1076.5
37.5°	966.0	977.7	1006.2	1036.3	1046.4
40°	924.1	937.5	967.7	1002.8	1016.2
42.5°	878.9	897.4	930.8	969.3	984.4
45°	833.7	850.5	892.3	935.9	952.6
47.5°	785.2	805.3	850.5	902.4	922.5
50°	733.3	758.4	810.3	867.2	889.0
52.5°	681.4	709.8	768.4	832.1	855.5
55°	631.2	657.9	728.3	796.9	822.0
57.5°	575.9	609.4	686.4	760.1	785.2
60°	519.0	555.8	644.6	721.6	748.4
62.5°	462.1	503.9	604.4	681.4	709.8
65°	405.1	452.0	557.5	639.5	668.0
67.5°	349.9	401.8	514.0	596.0	624.5
70°	286.3	351.6	467.1	547.5	575.9
72.5°	227.7	303.0	421.9	497.2	522.3
75°	175.8	256.1	371.7	440.3	450.4
77.5°	128.9	209.3	319.8	343.2	344.9
80°	87.1	167.4	244.4	241.1	244.4
82.5°	56.9	125.6	154.0	172.4	174.1
85°	33.5	73.7	90.4	100.4	102.1
87.5°	16.7	25.1	31.8	33.5	36.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)