

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P308347

Luminaire Tested: **22FCZ2-20HE-UNV-L82765-RDP-CA125-W2A-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P308347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-24)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 22FCZ2-20HE-UNV-L82765-RDP-CA125-W2A-U-6500K
Description: 2'X2' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" ACRYLIC SHEET
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1356.0 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 17.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P308347

CATALOG NUMBER: 22FCZ2-20HE-UNV-L82765-RDP-CA125-W2A-U-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P308347

CATALOG NUMBER: 22FCZ2-20HE-UNV-L82765-RDP-CA125-W2A-U-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	86	88	86	84	82
2	97	88	81	75	95	86	80	74	83	77	72	80	75	71	76	72	69	67
3	88	77	68	61	86	75	67	61	72	65	60	70	64	59	67	62	58	55
4	80	68	59	51	78	66	58	51	64	56	50	61	55	50	59	54	49	47
5	74	60	51	44	72	59	50	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	44	38	51	43	38	50	43	37	48	42	37	35
7	63	49	40	33	61	48	39	33	47	39	33	45	38	33	44	37	33	31
8	59	45	36	30	57	44	35	30	43	35	29	41	34	29	40	34	29	27
9	55	41	32	27	53	40	32	27	39	32	26	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1146	1146	1146
5°	1140	1148	1148
10°	1137	1145	1150
15°	1131	1142	1151
20°	1123	1140	1151
25°	1120	1143	1155
30°	1110	1134	1156
35°	1098	1130	1163
40°	1083	1128	1177
45°	1067	1128	1215
50°	1044	1136	1266
55°	1016	1161	1339
60°	982	1192	1433
65°	914	1251	1550
70°	840	1311	1696
75°	736	1380	1753
80°	634	1314	1376
85°	556	954	1047



TEST NUMBER: P308347

CATALOG NUMBER: 22FCZ2-20HE-UNV-L82765-RDP-CA125-W2A-U-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.3	3.0
10°-20°	115.7	8.5
20°-30°	176.5	13.0
30°-40°	215.5	15.9
40°-50°	230.4	17.0
50°-60°	222.4	16.4
60°-70°	191.5	14.1
70°-80°	129.5	9.6
80°-90°	34.2	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	332.5	24.5
0°-40°	548.0	40.4
0°-60°	1000.8	73.8
0°-90°	1356.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1356.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	426	426	426	426	426	
5°	422	423	425	425	425	40
15°	406	407	410	412	413	115
25°	377	379	385	387	389	174
35°	334	337	344	351	354	209
45°	280	285	296	311	319	216
55°	216	223	247	272	285	194
65°	144	158	196	227	243	143
75°	71	94	133	160	169	76
85°	18	25	31	32	34	20
90°	0	0	0	0	0	



TEST NUMBER: P308347

CATALOG NUMBER: 22FC22-20HE-UNV-L82765-RDP-CA125-W2A-U-6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	425.9	425.9	425.9	425.9	425.9
2.5°	423.0	423.9	425.9	425.9	426.9
5°	422.0	423.0	424.9	424.9	424.9
7.5°	419.0	420.0	422.0	423.0	423.0
10°	416.0	417.0	419.0	420.0	421.0
12.5°	411.0	412.0	415.0	417.0	417.0
15°	406.0	407.0	410.0	412.0	413.0
17.5°	400.0	402.0	405.0	407.0	408.0
20°	392.0	394.0	398.0	401.0	402.0
22.5°	385.0	387.0	391.0	394.0	396.0
25°	377.1	379.1	385.0	387.0	389.0
27.5°	367.1	369.1	374.1	378.1	381.1
30°	357.1	359.1	365.1	370.1	372.1
32.5°	346.1	349.1	356.1	360.1	363.1
35°	334.2	337.2	344.1	351.1	354.1
37.5°	322.2	325.2	332.2	341.2	345.1
40°	308.2	312.2	321.2	333.2	335.2
42.5°	295.3	300.3	308.2	322.2	327.2
45°	280.3	285.3	296.3	311.2	319.2
47.5°	266.3	271.3	283.3	301.3	311.2
50°	249.4	256.4	271.3	292.3	302.3
52.5°	233.4	239.4	259.4	282.3	294.3
55°	216.5	223.4	247.4	272.3	285.3
57.5°	201.5	207.5	234.4	262.3	277.3
60°	182.5	190.5	221.5	251.4	266.3
62.5°	162.6	174.6	208.5	239.4	255.4
65°	143.6	157.6	196.5	227.4	243.4
67.5°	126.7	141.6	181.5	214.5	229.4
70°	106.7	125.7	166.6	198.5	215.5
72.5°	88.8	109.7	149.6	181.5	196.5
75°	70.8	93.8	132.7	159.6	168.6
77.5°	54.9	76.8	113.7	121.7	122.7
80°	40.9	60.8	84.8	85.8	88.8
82.5°	27.9	42.9	54.9	59.9	60.8
85°	18.0	24.9	30.9	31.9	33.9
87.5°	8.0	9.0	11.0	10.0	10.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)