

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309611

Luminaire Tested: **24FCZ2-55HE-UNV-L82765-HRP-CP125-W2A-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309611
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-55HE-UNV-L82765-HRP-CP125-W2A-U-4000K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" POLYCARB SHEET
Light Source: (336) 4000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3754.0 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 43.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309611

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-HRP-CP125-W2A-U-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P309611

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-HRP-CP125-W2A-U-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1639	1639	1639
5°	1641	1634	1641
10°	1636	1634	1645
15°	1627	1631	1646
20°	1616	1627	1649
25°	1596	1619	1652
30°	1577	1614	1658
35°	1551	1606	1660
40°	1524	1596	1676
45°	1489	1594	1701
50°	1441	1592	1747
55°	1390	1604	1810
60°	1311	1628	1890
65°	1211	1666	1996
70°	1057	1725	2127
75°	858	1814	2198
80°	633	1778	1778
85°	485	1311	1480



TEST NUMBER: P309611

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-HRP-CP125-W2A-U-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	3.1
10°-20°	331.3	8.8
20°-30°	504.4	13.4
30°-40°	612.5	16.3
40°-50°	647.1	17.2
50°-60°	610.6	16.3
60°-70°	507.7	13.5
70°-80°	334.0	8.9
80°-90°	91.1	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	951.1	25.3
0°-40°	1563.6	41.7
0°-60°	2821.3	75.2
0°-90°	3754.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3754.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1215	1215	1210	1215	1215	115
15°	1168	1169	1171	1182	1182	329
25°	1075	1081	1091	1110	1113	496
35°	944	956	978	1003	1010	591
45°	783	798	838	878	894	603
55°	592	618	684	748	772	528
65°	380	424	523	600	627	376
75°	165	240	349	413	423	178
85°	31	69	85	94	96	38
90°	0	0	0	0	0	



TEST NUMBER: P309611

CATALOG NUMBER: 24FCZ2-55HE-UNV-L82765-HRP-CP125-W2A-U-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1218.0	1218.0	1218.0	1218.0	1218.0
2.5°	1219.6	1218.0	1211.7	1218.0	1218.0
5°	1214.8	1214.8	1210.1	1214.8	1214.8
7.5°	1207.0	1207.0	1203.8	1210.1	1210.1
10°	1197.6	1197.6	1196.0	1203.8	1203.8
12.5°	1183.4	1185.0	1183.4	1192.8	1192.8
15°	1167.7	1169.3	1170.8	1181.8	1181.8
17.5°	1147.3	1150.4	1153.6	1166.1	1167.7
20°	1128.4	1130.0	1136.3	1150.4	1152.0
22.5°	1103.3	1108.0	1115.8	1130.0	1134.7
25°	1075.0	1081.3	1090.7	1109.5	1112.7
27.5°	1048.3	1053.0	1065.5	1086.0	1092.3
30°	1015.3	1023.1	1038.8	1059.3	1067.1
32.5°	983.8	991.7	1010.5	1032.5	1038.8
35°	944.5	955.5	977.5	1002.7	1010.5
37.5°	906.8	917.8	944.5	972.8	982.2
40°	867.5	880.1	908.4	941.4	954.0
42.5°	825.1	842.4	873.8	910.0	924.1
45°	782.7	798.4	837.7	878.5	894.2
47.5°	737.1	755.9	798.4	847.1	866.0
50°	688.4	711.9	760.7	814.1	834.5
52.5°	639.6	666.4	721.4	781.1	803.1
55°	592.5	617.6	683.6	748.1	771.7
57.5°	540.6	572.1	644.4	713.5	737.1
60°	487.2	521.8	605.1	677.4	702.5
62.5°	433.8	473.1	567.3	639.6	666.4
65°	380.3	424.3	523.3	600.4	627.1
67.5°	328.5	377.2	482.5	559.5	586.2
70°	268.7	330.0	438.5	513.9	540.6
72.5°	213.7	284.5	396.0	466.8	490.3
75°	165.0	240.5	348.9	413.3	422.8
77.5°	121.0	196.4	300.2	322.2	323.7
80°	81.7	157.2	229.5	226.3	229.5
82.5°	53.4	117.9	144.6	161.9	163.4
85°	31.4	69.2	84.9	94.3	95.9
87.5°	15.7	23.6	29.9	31.4	34.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)