

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309701

Luminaire Tested: **24FCZ2-65HE-UNV-L82765-HRP-CP125-W2A-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309701
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-65HE-UNV-L82765-HRP-CP125-W2A-U-4000K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" POLYCARB SHEET
Light Source: (336) 4000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4421.0 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 53.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309701

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CP125-W2A-U-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P309701

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CP125-W2A-U-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1930	1930	1930
5°	1932	1925	1932
10°	1927	1924	1937
15°	1916	1921	1939
20°	1903	1916	1943
25°	1879	1907	1945
30°	1858	1901	1952
35°	1827	1891	1955
40°	1795	1879	1973
45°	1754	1877	2004
50°	1697	1875	2057
55°	1637	1889	2132
60°	1544	1918	2226
65°	1426	1962	2351
70°	1245	2031	2505
75°	1010	2136	2588
80°	745	2094	2094
85°	571	1542	1743



TEST NUMBER: P309701

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CP125-W2A-U-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.9	3.1
10°-20°	390.2	8.8
20°-30°	594.0	13.4
30°-40°	721.3	16.3
40°-50°	762.0	17.2
50°-60°	719.1	16.3
60°-70°	597.9	13.5
70°-80°	393.4	8.9
80°-90°	107.2	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1120.1	25.3
0°-40°	1841.4	41.7
0°-60°	3322.6	75.2
0°-90°	4421.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4421.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1434	1434	1434	1434	1434	
5°	1431	1431	1425	1431	1431	136
15°	1375	1377	1379	1392	1392	388
25°	1266	1273	1284	1307	1310	584
35°	1112	1125	1151	1181	1190	696
45°	922	940	986	1035	1053	710
55°	698	727	805	881	909	622
65°	448	500	616	707	738	443
75°	194	283	411	487	498	209
85°	37	81	100	111	113	45
90°	0	0	0	0	0	



TEST NUMBER: P309701

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CP125-W2A-U-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1434.4	1434.4	1434.4	1434.4	1434.4
2.5°	1436.2	1434.4	1427.0	1434.4	1434.4
5°	1430.7	1430.7	1425.1	1430.7	1430.7
7.5°	1421.4	1421.4	1417.7	1425.1	1425.1
10°	1410.3	1410.3	1408.5	1417.7	1417.7
12.5°	1393.7	1395.5	1393.7	1404.8	1404.8
15°	1375.2	1377.0	1378.9	1391.8	1391.8
17.5°	1351.1	1354.8	1358.5	1373.3	1375.2
20°	1328.9	1330.8	1338.2	1354.8	1356.7
22.5°	1299.3	1304.8	1314.1	1330.8	1336.3
25°	1266.0	1273.4	1284.5	1306.7	1310.4
27.5°	1234.5	1240.1	1254.9	1278.9	1286.3
30°	1195.6	1204.9	1223.4	1247.5	1256.7
32.5°	1158.6	1167.9	1190.1	1216.0	1223.4
35°	1112.4	1125.3	1151.2	1180.8	1190.1
37.5°	1067.9	1080.9	1112.4	1145.7	1156.8
40°	1021.7	1036.5	1069.8	1108.6	1123.5
42.5°	971.7	992.0	1029.1	1071.6	1088.3
45°	921.7	940.2	986.5	1034.6	1053.1
47.5°	868.0	890.3	940.2	997.6	1019.8
50°	810.7	838.4	895.8	958.7	982.8
52.5°	753.3	784.8	849.5	919.9	945.8
55°	697.8	727.4	805.1	881.0	908.8
57.5°	636.7	673.7	758.8	840.3	868.0
60°	573.8	614.5	712.6	797.7	827.3
62.5°	510.8	557.1	668.2	753.3	784.8
65°	447.9	499.7	616.3	707.0	738.5
67.5°	386.8	444.2	568.2	658.9	690.4
70°	316.5	388.7	516.4	605.2	636.7
72.5°	251.7	335.0	466.4	549.7	577.5
75°	194.3	283.2	410.9	486.8	497.9
77.5°	142.5	231.4	353.5	379.4	381.3
80°	96.2	185.1	270.2	266.5	270.2
82.5°	62.9	138.8	170.3	190.6	192.5
85°	37.0	81.4	99.9	111.1	112.9
87.5°	18.5	27.8	35.2	37.0	40.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)