

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P308425

Luminaire Tested: **22FCZ2-29HE-UNV-L82765-RDP-CA08-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P308425
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-24)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 22FCZ2-29HE-UNV-L82765-RDP-CA08-W2A-U-5000K
Description: 2'X2' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.08" ACRYLIC SHEET
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1769.0 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P308425

CATALOG NUMBER: 22FCZ2-29HE-UNV-L82765-RDP-CA08-W2A-U-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P308425

CATALOG NUMBER: 22FCZ2-29HE-UNV-L82765-RDP-CA08-W2A-U-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	86	88	86	84	82
2	97	88	81	75	95	86	80	74	83	77	72	80	75	71	76	72	69	67
3	88	77	68	61	86	75	67	61	72	65	60	70	64	59	67	62	58	55
4	80	68	59	51	78	66	58	51	64	56	50	61	55	50	59	54	49	47
5	74	60	51	44	72	59	50	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	44	38	51	43	38	50	43	37	48	42	37	35
7	63	49	40	33	61	48	39	33	47	39	33	45	38	33	44	37	33	31
8	59	45	36	30	57	44	35	30	43	35	29	41	34	29	40	34	29	27
9	55	41	32	27	53	40	32	27	39	32	26	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1495	1495	1495
5°	1487	1498	1498
10°	1483	1494	1501
15°	1475	1490	1501
20°	1464	1487	1502
25°	1461	1491	1507
30°	1448	1480	1508
35°	1432	1475	1518
40°	1413	1472	1536
45°	1392	1471	1585
50°	1362	1482	1651
55°	1325	1514	1746
60°	1281	1555	1870
65°	1193	1633	2022
70°	1095	1710	2212
75°	961	1800	2286
80°	828	1714	1795
85°	722	1244	1365



TEST NUMBER: P308425

CATALOG NUMBER: 22FCZ2-29HE-UNV-L82765-RDP-CA08-W2A-U-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	3.0
10°-20°	150.9	8.5
20°-30°	230.2	13.0
30°-40°	281.2	15.9
40°-50°	300.6	17.0
50°-60°	290.2	16.4
60°-70°	249.8	14.1
70°-80°	169.0	9.6
80°-90°	44.6	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	433.7	24.5
0°-40°	714.9	40.4
0°-60°	1305.6	73.8
0°-90°	1769.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1769.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	556	556	556	556	556	
5°	550	552	554	554	554	52
15°	530	531	535	538	539	149
25°	492	494	502	505	508	226
35°	436	440	449	458	462	273
45°	366	372	386	406	416	282
55°	282	292	323	355	372	253
65°	187	206	256	297	318	186
75°	92	122	173	208	220	99
85°	23	32	40	42	44	26
90°	0	0	0	0	0	



TEST NUMBER: P308425

CATALOG NUMBER: 22FC22-29HE-UNV-L82765-RDP-CA08-W2A-U-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	555.7	555.7	555.7	555.7	555.7
2.5°	551.8	553.1	555.7	555.7	557.0
5°	550.5	551.8	554.4	554.4	554.4
7.5°	546.6	547.9	550.5	551.8	551.8
10°	542.7	544.0	546.6	547.9	549.2
12.5°	536.2	537.5	541.4	544.0	544.0
15°	529.6	530.9	534.9	537.5	538.8
17.5°	521.8	524.4	528.3	530.9	532.2
20°	511.4	514.0	519.2	523.1	524.4
22.5°	502.3	504.9	510.1	514.0	516.6
25°	491.9	494.5	502.3	504.9	507.5
27.5°	478.9	481.5	488.0	493.2	497.1
30°	465.9	468.5	476.3	482.8	485.4
32.5°	451.6	455.5	464.6	469.8	473.7
35°	436.0	439.9	449.0	458.1	462.0
37.5°	420.3	424.2	433.3	445.1	450.3
40°	402.1	407.3	419.0	434.6	437.3
42.5°	385.2	391.7	402.1	420.3	426.8
45°	365.7	372.2	386.5	406.0	416.4
47.5°	347.5	354.0	369.6	393.0	406.0
50°	325.3	334.4	354.0	381.3	394.3
52.5°	304.5	312.3	338.3	368.3	383.9
55°	282.4	291.5	322.7	355.3	372.2
57.5°	262.9	270.7	305.8	342.3	361.8
60°	238.1	248.6	288.9	327.9	347.5
62.5°	212.1	227.7	272.0	312.3	333.1
65°	187.4	205.6	256.4	296.7	317.5
67.5°	165.3	184.8	236.8	279.8	299.3
70°	139.2	164.0	217.3	259.0	281.1
72.5°	115.8	143.1	195.2	236.8	256.4
75°	92.4	122.3	173.1	208.2	219.9
77.5°	71.6	100.2	148.4	158.8	160.1
80°	53.4	79.4	110.6	111.9	115.8
82.5°	36.4	56.0	71.6	78.1	79.4
85°	23.4	32.5	40.3	41.6	44.2
87.5°	10.4	11.7	14.3	13.0	13.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)