

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309715

Luminaire Tested: **24FCZ2-65HE-UNV-L82765-HRP-CP187-W2A-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P309715  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 24FCZ2-65HE-UNV-L82765-HRP-CP187-W2A-U-6500K  
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.187"  
POLYCARB SHEET  
Light Source: (336) 6500K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4434.0 lumens  
Efficiency: N/A  
Efficacy: 80.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 54.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P309715

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CP187-W2A-U-6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P309715

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CP187-W2A-U-6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1936	1936	1936
5°	1938	1930	1938
10°	1933	1930	1943
15°	1921	1926	1944
20°	1908	1922	1948
25°	1885	1913	1951
30°	1863	1906	1958
35°	1832	1896	1961
40°	1800	1884	1979
45°	1759	1883	2010
50°	1702	1881	2063
55°	1642	1894	2138
60°	1548	1923	2233
65°	1430	1968	2358
70°	1249	2037	2512
75°	1013	2142	2596
80°	748	2100	2100
85°	573	1547	1748



TEST NUMBER: P309715

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CP187-W2A-U-6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.3	3.1
10°-20°	391.4	8.8
20°-30°	595.8	13.4
30°-40°	723.4	16.3
40°-50°	764.3	17.2
50°-60°	721.2	16.3
60°-70°	599.6	13.5
70°-80°	394.5	8.9
80°-90°	107.5	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1123.4	25.3
0°-40°	1846.8	41.7
0°-60°	3332.3	75.2
0°-90°	4434.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4434.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1439	1439	1439	1439	1439	
5°	1435	1435	1429	1435	1435	136
15°	1379	1381	1383	1396	1396	389
25°	1270	1277	1288	1310	1314	586
35°	1116	1129	1155	1184	1194	698
45°	924	943	989	1038	1056	712
55°	700	730	808	884	911	623
65°	449	501	618	709	741	444
75°	195	284	412	488	499	210
85°	37	82	100	111	113	45
90°	0	0	0	0	0	



TEST NUMBER: P309715

CATALOG NUMBER: 24FCZ2-65HE-UNV-L82765-HRP-CP187-W2A-U-6500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1438.6	1438.6	1438.6	1438.6	1438.6
2.5°	1440.5	1438.6	1431.2	1438.6	1438.6
5°	1434.9	1434.9	1429.3	1434.9	1434.9
7.5°	1425.6	1425.6	1421.9	1429.3	1429.3
10°	1414.5	1414.5	1412.6	1421.9	1421.9
12.5°	1397.8	1399.6	1397.8	1408.9	1408.9
15°	1379.2	1381.1	1382.9	1395.9	1395.9
17.5°	1355.1	1358.8	1362.5	1377.4	1379.2
20°	1332.8	1334.7	1342.1	1358.8	1360.7
22.5°	1303.1	1308.7	1318.0	1334.7	1340.2
25°	1269.7	1277.1	1288.3	1310.5	1314.2
27.5°	1238.1	1243.7	1258.6	1282.7	1290.1
30°	1199.2	1208.4	1227.0	1251.1	1260.4
32.5°	1162.0	1171.3	1193.6	1219.6	1227.0
35°	1115.6	1128.6	1154.6	1184.3	1193.6
37.5°	1071.1	1084.1	1115.6	1149.0	1160.2
40°	1024.7	1039.5	1072.9	1111.9	1126.8
42.5°	974.5	995.0	1032.1	1074.8	1091.5
45°	924.4	943.0	989.4	1037.7	1056.2
47.5°	870.6	892.9	943.0	1000.5	1022.8
50°	813.0	840.9	898.4	961.6	985.7
52.5°	755.5	787.1	852.0	922.6	948.6
55°	699.8	729.5	807.5	883.6	911.4
57.5°	638.6	675.7	761.1	842.7	870.6
60°	575.4	616.3	714.7	800.1	829.8
62.5°	512.3	558.7	670.1	755.5	787.1
65°	449.2	501.2	618.1	709.1	740.7
67.5°	388.0	445.5	569.9	660.8	692.4
70°	317.4	389.8	517.9	607.0	638.6
72.5°	252.5	336.0	467.8	551.3	579.2
75°	194.9	284.0	412.1	488.2	499.3
77.5°	142.9	232.0	354.5	380.5	382.4
80°	96.5	185.6	271.0	267.3	271.0
82.5°	63.1	139.2	170.8	191.2	193.1
85°	37.1	81.7	100.2	111.4	113.2
87.5°	18.6	27.8	35.3	37.1	40.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)