

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P308503

Luminaire Tested: **22FCZ2-34HE-UNV-L82765-RDP-CP250-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P308503  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-24)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 22FCZ2-34HE-UNV-L82765-RDP-CP250-W2A-U-3500K  
Description: 2'X2' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.250" POLYCARB SHEET  
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1878.0 lumens  
Efficiency: N/A  
Efficacy: 67.8 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.3 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P308503

CATALOG NUMBER: 22FCZ2-34HE-UNV-L82765-RDP-CP250-W2A-U-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P308503

CATALOG NUMBER: 22FCZ2-34HE-UNV-L82765-RDP-CP250-W2A-U-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	86	88	86	84	82
2	97	88	81	75	95	86	80	74	83	77	72	80	75	71	76	72	69	67
3	88	77	68	61	86	75	67	61	72	65	60	70	64	59	67	62	58	55
4	80	68	59	51	78	66	58	51	64	56	50	61	55	50	59	54	49	47
5	74	60	51	44	72	59	50	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	44	38	51	43	38	50	43	37	48	42	37	35
7	63	49	40	33	61	48	39	33	47	39	33	45	38	33	44	37	33	31
8	59	45	36	30	57	44	35	30	43	35	29	41	34	29	40	34	29	27
9	55	41	32	27	53	40	32	27	39	32	26	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1587	1587	1587
5°	1579	1590	1590
10°	1574	1585	1593
15°	1567	1582	1594
20°	1555	1578	1594
25°	1550	1583	1600
30°	1537	1571	1601
35°	1520	1566	1611
40°	1500	1563	1631
45°	1477	1561	1682
50°	1446	1573	1752
55°	1407	1607	1854
60°	1361	1651	1985
65°	1266	1733	2146
70°	1163	1815	2348
75°	1020	1910	2428
80°	877	1819	1906
85°	769	1321	1451



TEST NUMBER: P308503

CATALOG NUMBER: 22FCZ2-34HE-UNV-L82765-RDP-CP250-W2A-U-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.8	3.0
10°-20°	160.2	8.5
20°-30°	244.4	13.0
30°-40°	298.5	15.9
40°-50°	319.1	17.0
50°-60°	308.0	16.4
60°-70°	265.2	14.1
70°-80°	179.4	9.6
80°-90°	47.3	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	460.5	24.5
0°-40°	758.9	40.4
0°-60°	1386.1	73.8
0°-90°	1878.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1878.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	584	586	588	588	588	55
15°	562	564	568	571	572	159
25°	522	525	533	536	539	240
35°	463	467	477	486	490	290
45°	388	395	410	431	442	300
55°	300	310	343	377	395	269
65°	199	218	272	315	337	198
75°	98	130	184	221	234	105
85°	25	34	43	44	47	28
90°	0	0	0	0	0	



TEST NUMBER: P308503

CATALOG NUMBER: 22FCZ2-34HE-UNV-L82765-RDP-CP250-W2A-U-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	589.9	589.9	589.9	589.9	589.9
2.5°	585.8	587.1	589.9	589.9	591.3
5°	584.4	585.8	588.5	588.5	588.5
7.5°	580.2	581.6	584.4	585.8	585.8
10°	576.1	577.5	580.2	581.6	583.0
12.5°	569.2	570.6	574.7	577.5	577.5
15°	562.3	563.7	567.8	570.6	572.0
17.5°	554.0	556.8	560.9	563.7	565.0
20°	542.9	545.7	551.2	555.4	556.8
22.5°	533.3	536.0	541.6	545.7	548.5
25°	522.2	525.0	533.3	536.0	538.8
27.5°	508.4	511.2	518.1	523.6	527.7
30°	494.6	497.4	505.6	512.5	515.3
32.5°	479.4	483.5	493.2	498.7	502.9
35°	462.8	467.0	476.6	486.3	490.4
37.5°	446.2	450.4	460.0	472.5	478.0
40°	426.9	432.4	444.9	461.4	464.2
42.5°	408.9	415.8	426.9	446.2	453.1
45°	388.2	395.1	410.3	431.0	442.1
47.5°	368.9	375.8	392.4	417.2	431.0
50°	345.4	355.1	375.8	404.8	418.6
52.5°	323.3	331.6	359.2	391.0	407.6
55°	299.8	309.5	342.6	377.2	395.1
57.5°	279.1	287.4	324.7	363.3	384.1
60°	252.8	263.9	306.7	348.1	368.9
62.5°	225.2	241.8	288.7	331.6	353.7
65°	198.9	218.3	272.2	315.0	337.1
67.5°	175.5	196.2	251.4	297.0	317.8
70°	147.8	174.1	230.7	274.9	298.4
72.5°	123.0	152.0	207.2	251.4	272.2
75°	98.1	129.9	183.7	221.0	233.5
77.5°	76.0	106.4	157.5	168.5	169.9
80°	56.6	84.3	117.4	118.8	123.0
82.5°	38.7	59.4	76.0	82.9	84.3
85°	24.9	34.5	42.8	44.2	47.0
87.5°	11.1	12.4	15.2	13.8	13.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)