

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309928

Luminaire Tested: **24FCZ2-35HE-UNV-L82765-RDP-CP125-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309928
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-35HE-UNV-L82765-RDP-CP125-W2A-U-5000K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" POLYCARB SHEET
Light Source: (336) 5000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2177.0 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309928

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-RDP-CP125-W2A-U-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P309928

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-RDP-CP125-W2A-U-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	921	921	921
5°	925	919	923
10°	922	919	924
15°	920	919	925
20°	914	918	928
25°	910	920	930
30°	903	918	933
35°	894	915	936
40°	884	914	948
45°	869	914	970
50°	850	920	999
55°	828	935	1044
60°	793	953	1101
65°	742	987	1169
70°	675	1032	1257
75°	572	1089	1314
80°	452	1096	1062
85°	333	834	934



TEST NUMBER: P309928

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-RDP-CP125-W2A-U-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.9	3.0
10°-20°	186.9	8.6
20°-30°	285.8	13.1
30°-40°	349.4	16.0
40°-50°	372.4	17.1
50°-60°	356.1	16.4
60°-70°	301.6	13.9
70°-80°	202.7	9.3
80°-90°	57.2	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	537.7	24.7
0°-40°	887.0	40.7
0°-60°	1615.5	74.2
0°-90°	2177.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2177.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	685	685	685	685	685	
5°	685	684	680	684	684	65
15°	661	661	660	665	664	186
25°	613	616	620	625	626	283
35°	544	548	557	568	570	341
45°	457	464	480	501	510	352
55°	353	366	398	430	445	315
65°	233	257	310	351	367	232
75°	110	150	210	245	253	118
85°	22	44	54	58	60	27
90°	0	0	0	0	0	



TEST NUMBER: P309928

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-RDP-CP125-W2A-U-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	684.6	684.6	684.6	684.6	684.6
2.5°	685.7	685.7	682.4	684.6	684.6
5°	684.6	683.5	680.3	683.5	683.5
7.5°	681.4	680.3	678.1	681.4	680.3
10°	674.9	674.9	672.7	676.0	676.0
12.5°	669.5	668.4	667.3	671.6	670.6
15°	660.8	660.8	659.8	665.2	664.1
17.5°	650.1	651.1	652.2	656.5	657.6
20°	638.2	640.3	641.4	647.9	647.9
22.5°	627.4	628.5	630.6	637.1	637.1
25°	613.3	615.5	619.8	625.2	626.3
27.5°	599.3	600.4	605.8	613.3	614.4
30°	580.9	584.2	590.7	599.3	600.4
32.5°	564.7	568.0	575.5	584.2	586.3
35°	544.2	548.5	557.2	568.0	570.1
37.5°	525.9	529.1	539.9	551.8	555.0
40°	503.2	509.7	520.5	534.5	539.9
42.5°	480.5	487.0	500.0	518.3	524.8
45°	456.8	464.3	480.5	501.0	509.7
47.5°	433.0	441.6	460.0	483.8	493.5
50°	406.0	416.8	439.5	466.5	477.3
52.5°	380.1	393.1	417.9	448.1	462.2
55°	353.1	366.1	398.5	429.8	444.9
57.5°	322.9	340.1	375.8	411.4	427.6
60°	294.8	311.0	354.2	393.1	409.3
62.5°	264.6	286.2	332.6	373.6	389.8
65°	233.2	257.0	309.9	350.9	367.1
67.5°	205.2	231.1	287.2	328.3	344.5
70°	171.7	204.1	262.4	303.4	319.6
72.5°	140.4	176.0	236.5	276.4	291.6
75°	110.1	150.1	209.5	245.1	252.7
77.5°	82.1	124.2	181.4	196.5	191.1
80°	58.3	99.3	141.5	133.9	137.1
82.5°	37.8	75.6	87.5	99.3	102.6
85°	21.6	44.3	54.0	58.3	60.5
87.5°	9.7	16.2	21.6	21.6	20.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)