

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310024

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-RDP-CP187-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310024
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L82765-RDP-CP187-W2A-U-3500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.187" POLYCARB SHEET
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2289.0 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 30.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310024

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP187-W2A-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P310024

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP187-W2A-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	968	968	968
5°	972	966	971
10°	969	966	971
15°	968	966	973
20°	961	966	975
25°	957	968	978
30°	949	965	981
35°	940	962	985
40°	929	961	997
45°	914	961	1020
50°	894	967	1050
55°	871	983	1097
60°	834	1002	1158
65°	781	1038	1229
70°	710	1085	1322
75°	602	1145	1381
80°	475	1152	1117
85°	350	877	982



TEST NUMBER: P310024

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP187-W2A-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.3	3.0
10°-20°	196.5	8.6
20°-30°	300.5	13.1
30°-40°	367.4	16.0
40°-50°	391.5	17.1
50°-60°	374.4	16.4
60°-70°	317.1	13.9
70°-80°	213.1	9.3
80°-90°	60.1	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.3	24.7
0°-40°	932.7	40.7
0°-60°	1698.6	74.2
0°-90°	2289.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2289.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	720	720	720	720	720	
5°	720	719	715	719	719	68
15°	695	695	694	699	698	196
25°	645	647	652	657	658	297
35°	572	577	586	597	600	358
45°	480	488	505	527	536	370
55°	371	385	419	452	468	331
65°	245	270	326	369	386	243
75°	116	158	220	258	266	124
85°	23	47	57	61	64	28
90°	0	0	0	0	0	



TEST NUMBER: P310024

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP187-W2A-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	719.8	719.8	719.8	719.8	719.8
2.5°	721.0	721.0	717.6	719.8	719.8
5°	719.8	718.7	715.3	718.7	718.7
7.5°	716.4	715.3	713.0	716.4	715.3
10°	709.6	709.6	707.3	710.7	710.7
12.5°	703.9	702.8	701.7	706.2	705.1
15°	694.8	694.8	693.7	699.4	698.3
17.5°	683.5	684.6	685.8	690.3	691.4
20°	671.0	673.3	674.4	681.2	681.2
22.5°	659.7	660.8	663.1	669.9	669.9
25°	644.9	647.2	651.7	657.4	658.5
27.5°	630.1	631.3	636.9	644.9	646.0
30°	610.8	614.2	621.0	630.1	631.3
32.5°	593.8	597.2	605.2	614.2	616.5
35°	572.2	576.8	585.9	597.2	599.5
37.5°	552.9	556.3	567.7	580.2	583.6
40°	529.1	535.9	547.2	562.0	567.7
42.5°	505.2	512.1	525.7	545.0	551.8
45°	480.3	488.2	505.2	526.8	535.9
47.5°	455.3	464.4	483.7	508.6	518.9
50°	426.9	438.3	462.1	490.5	501.8
52.5°	399.7	413.3	439.4	471.2	485.9
55°	371.3	384.9	419.0	451.9	467.8
57.5°	339.5	357.6	395.1	432.6	449.6
60°	310.0	327.0	372.4	413.3	430.3
62.5°	278.2	300.9	349.7	392.8	409.9
65°	245.2	270.2	325.9	369.0	386.0
67.5°	215.7	243.0	302.0	345.2	362.2
70°	180.5	214.6	275.9	319.0	336.1
72.5°	147.6	185.1	248.6	290.7	306.6
75°	115.8	157.8	220.3	257.7	265.7
77.5°	86.3	130.6	190.7	206.6	201.0
80°	61.3	104.5	148.7	140.8	144.2
82.5°	39.7	79.5	92.0	104.5	107.9
85°	22.7	46.6	56.8	61.3	63.6
87.5°	10.2	17.0	22.7	22.7	21.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)