

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309077

Luminaire Tested: **22FCZ2-39HE-UNV-L82765-S-CP187-W2A-U-2700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P309077  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-23)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: 22FCZ2-39HE-UNV-L82765-S-CP187-W2A-U-2700K  
Description: 2'X2' TROFFER LED MODULE, SMOOTH LENS, 0.187" POLYCARB SHEET  
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: 

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3212.0 lumens  
Efficiency: N/A  
Efficacy: 99.1 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.26 / 1.34  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 32.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P309077

CATALOG NUMBER: 22FCZ2-39HE-UNV-L82765-S-CP187-W2A-U-2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P309077

CATALOG NUMBER: 22FCZ2-39HE-UNV-L82765-S-CP187-W2A-U-2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	94	97	94	91	93	90	88	89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	90	79	71	64	87	77	70	63	74	68	62	72	66	61	69	64	60	58
4	82	70	61	54	80	69	60	54	66	59	53	64	57	52	61	56	52	49
5	75	62	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	43
6	70	56	47	41	68	55	47	41	53	46	40	52	45	40	50	44	39	37
7	65	51	42	36	63	50	42	36	49	41	36	47	40	35	46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	31	30
9	56	43	35	29	55	42	34	29	41	34	29	40	33	29	39	33	28	27
10	53	40	32	26	51	39	31	26	38	31	26	37	31	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3097	3097	3097
5°	3077	3101	3109
10°	3059	3088	3104
15°	3019	3060	3090
20°	2970	3030	3077
25°	2910	2999	3057
30°	2836	2938	3031
35°	2757	2885	3003
40°	2664	2827	2974
45°	2567	2760	2943
50°	2472	2685	2918
55°	2355	2637	2897
60°	2250	2573	2887
65°	2099	2557	2920
70°	1934	2535	3007
75°	1745	2571	3163
80°	1509	2647	2972
85°	1250	2220	2220



TEST NUMBER: P309077

CATALOG NUMBER: 22FCZ2-39HE-UNV-L82765-S-CP187-W2A-U-2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.8	3.4
10°-20°	309.7	9.6
20°-30°	463.5	14.4
30°-40°	548.9	17.1
40°-50°	559.4	17.4
50°-60°	501.3	15.6
60°-70°	392.5	12.2
70°-80°	253.1	7.9
80°-90°	74.8	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	882.1	27.5
0°-40°	1430.9	44.5
0°-60°	2491.6	77.6
0°-90°	3212.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3212.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1151	1151	1151	1151	1151	
5°	1139	1142	1148	1150	1151	108
15°	1084	1090	1098	1108	1109	305
25°	980	989	1010	1024	1030	451
35°	839	850	878	905	914	525
45°	674	689	725	763	773	521
55°	502	518	562	601	617	450
65°	330	349	402	441	459	328
75°	168	193	247	289	304	180
85°	40	55	72	72	72	47
90°	0	0	0	0	0	



TEST NUMBER: P309077

CATALOG NUMBER: 22FCZ2-39HE-UNV-L82765-S-CP187-W2A-U-2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1151.0	1151.0	1151.0	1151.0	1151.0
2.5°	1143.5	1146.5	1152.5	1154.0	1154.0
5°	1139.0	1142.0	1148.0	1149.5	1151.0
7.5°	1131.5	1133.0	1140.5	1143.5	1145.0
10°	1119.5	1122.5	1130.0	1134.5	1136.0
12.5°	1103.0	1107.5	1116.5	1122.5	1124.0
15°	1083.5	1089.5	1098.5	1107.5	1109.0
17.5°	1062.5	1068.5	1080.5	1091.0	1094.0
20°	1037.1	1044.6	1058.0	1070.0	1074.5
22.5°	1011.6	1017.6	1034.1	1049.1	1053.5
25°	980.1	989.1	1010.1	1023.6	1029.6
27.5°	947.1	957.6	978.6	996.6	1002.6
30°	912.7	923.2	945.6	968.1	975.6
32.5°	876.7	888.7	915.7	938.2	945.6
35°	839.2	849.7	878.2	905.2	914.2
37.5°	800.3	809.3	842.2	870.7	879.7
40°	758.3	770.3	804.8	837.7	846.7
42.5°	716.4	729.8	764.3	800.3	809.3
45°	674.4	689.4	725.3	762.8	773.3
47.5°	633.9	645.9	686.4	722.3	737.3
50°	590.5	602.5	641.4	681.9	696.9
52.5°	545.5	562.0	604.0	642.9	660.9
55°	502.0	518.5	562.0	601.0	617.4
57.5°	461.6	475.1	520.0	560.5	577.0
60°	418.1	430.1	478.1	521.5	536.5
62.5°	371.7	389.6	439.1	479.6	497.6
65°	329.7	349.2	401.6	440.6	458.6
67.5°	290.7	308.7	359.7	401.6	421.1
70°	245.8	269.8	322.2	364.2	382.2
72.5°	209.8	230.8	284.7	326.7	346.2
75°	167.8	193.3	247.3	289.2	304.2
77.5°	133.4	158.9	209.8	242.8	250.3
80°	97.4	122.9	170.8	187.3	191.8
82.5°	65.9	89.9	122.9	127.4	128.9
85°	40.5	55.4	71.9	71.9	71.9
87.5°	19.5	22.5	25.5	24.0	24.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)