

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309153

Luminaire Tested: **24FCZ2-30HE-UNV-L82765-HRP-CA125-W2A-U-4500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-30HE-UNV-L82765-HRP-CA125-W2A-U-4500K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 4500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2155.0 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 21.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309153

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-HRP-CA125-W2A-U-4500K

Luminous Intensity Polar Plot





TEST NUMBER: P309153

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-HRP-CA125-W2A-U-4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	941	941	941
5°	942	938	942
10°	939	938	944
15°	934	936	945
20°	928	934	947
25°	916	929	948
30°	905	926	952
35°	891	922	953
40°	875	916	962
45°	855	915	977
50°	827	914	1003
55°	798	920	1039
60°	753	935	1085
65°	695	956	1146
70°	607	990	1221
75°	492	1041	1262
80°	363	1020	1020
85°	278	752	849



TEST NUMBER: P309153

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-HRP-CA125-W2A-U-4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.2	3.1
10°-20°	190.2	8.8
20°-30°	289.6	13.4
30°-40°	351.6	16.3
40°-50°	371.5	17.2
50°-60°	350.5	16.3
60°-70°	291.4	13.5
70°-80°	191.7	8.9
80°-90°	52.2	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	546.0	25.3
0°-40°	897.6	41.7
0°-60°	1619.6	75.2
0°-90°	2155.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2155.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	699	699	699	699	699	
5°	697	697	695	697	697	66
15°	670	671	672	678	678	189
25°	617	621	626	637	639	285
35°	542	548	561	576	580	339
45°	449	458	481	504	513	346
55°	340	355	392	429	443	303
65°	218	244	300	345	360	216
75°	95	138	200	237	243	102
85°	18	40	49	54	55	22
90°	0	0	0	0	0	



TEST NUMBER: P309153

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-HRP-CA125-W2A-U-4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	699.2	699.2	699.2	699.2	699.2
2.5°	700.1	699.2	695.6	699.2	699.2
5°	697.4	697.4	694.7	697.4	697.4
7.5°	692.9	692.9	691.1	694.7	694.7
10°	687.5	687.5	686.6	691.1	691.1
12.5°	679.3	680.2	679.3	684.8	684.8
15°	670.3	671.2	672.1	678.4	678.4
17.5°	658.6	660.4	662.2	669.4	670.3
20°	647.8	648.7	652.3	660.4	661.3
22.5°	633.3	636.0	640.5	648.7	651.4
25°	617.1	620.7	626.1	636.9	638.7
27.5°	601.8	604.5	611.7	623.4	627.0
30°	582.8	587.3	596.3	608.1	612.6
32.5°	564.8	569.3	580.1	592.7	596.3
35°	542.2	548.5	561.2	575.6	580.1
37.5°	520.6	526.9	542.2	558.5	563.9
40°	498.0	505.2	521.5	540.4	547.6
42.5°	473.6	483.6	501.6	522.4	530.5
45°	449.3	458.3	480.9	504.3	513.3
47.5°	423.1	433.9	458.3	486.3	497.1
50°	395.2	408.7	436.7	467.3	479.1
52.5°	367.2	382.5	414.1	448.4	461.0
55°	340.1	354.6	392.4	429.4	443.0
57.5°	310.4	328.4	369.9	409.6	423.1
60°	279.7	299.5	347.3	388.8	403.3
62.5°	249.0	271.6	325.7	367.2	382.5
65°	218.3	243.6	300.4	344.6	360.0
67.5°	188.6	216.5	277.0	321.2	336.5
70°	154.3	189.5	251.7	295.0	310.4
72.5°	122.7	163.3	227.3	267.9	281.5
75°	94.7	138.0	200.3	237.3	242.7
77.5°	69.5	112.8	172.3	184.9	185.8
80°	46.9	90.2	131.7	129.9	131.7
82.5°	30.7	67.7	83.0	92.9	93.8
85°	18.0	39.7	48.7	54.1	55.0
87.5°	9.0	13.5	17.1	18.0	19.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)